

# Floor standing unit

FXLQ-P



Multi tenant

## For perimeter zone air conditioning

- › Unit can be installed as free standing model by use of optional back plate
- › Its low height enables the unit to fit perfectly beneath a window
- › Stylish modern casing finished in pure white (RAL9010) and iron grey (RAL7011) blends easily with any interior
- › Requires very little installation space
- › Wall mounted installation facilitates cleaning beneath the unit where dust tends to accumulate


# FXLQ-P



Indoor unit				FXLQ	20P	25P	32P	40P	50P	63P
Cooling capacity	Nom.		kW		2.2	2.8	3.6	4.5	5.6	7.1
Heating capacity	Nom.		kW		2.5	3.2	4.0	5.0	6.3	8.000
Power input - 50Hz	Cooling	Nom.	kW		0.049			0.090		0.110
	Heating	Nom.	kW		0.049			0.090		0.110
Dimensions	Unit	Height	mm					600		
		Width	mm		1,000			1,140		1,420
		Depth	mm					232		
Weight	Unit		kg		27		32		38	
Casing	Colour				Fresh white (RAL9010) / Dark grey (RAL7011)					
Fan-Air flow rate - 50Hz	Cooling	High/Low	m <sup>3</sup> /min		7/6		8/6	11/8.5	14/11	16/12
Air filter	Type				Resin net					
Sound power level	Cooling	Nom.	dBA					-		
Sound pressure level	Cooling	High/Low	dBA			35/32		38/33	39/34	40/35
Refrigerant	Type/ GWP				R-410A / 2.087,5					
Piping connections	Liquid	OD	mm				6.35			9.52
	Gas	OD	mm				12.7			15.9
	Drain						O.D. 21 (Vinyl chloride)			
Power supply	Phase/Frequency/Voltage		Hz/V		1~/50/60/220-240/220					
Current - 50Hz	Maximum fuse amps (MFA)		A		15					
Control systems	Infrared remote control				BRC4C65					
	Simplified wired remote control for hotel applications				BRC2E52C (heat recovery type) / BRC3E52C (heat pump type)					
	Wired remote control				BRC1D52 / BRC1E52A/B					

Contains fluorinated greenhouse gases

**Daikin Europe N.V.** Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · [www.daikin.eu](http://www.daikin.eu) · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-248

02/15



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.