

# Remote Controller Setup Instructions


## CAUTION

1. No switch box or staple is supplied. Prepare them locally.
2. No remote controller cord is supplied. Prepare the optional remote controller cord 4 wire.
3. Be sure to turn off the power to any apparatus connected prior to mounting.
4. Prior to mounting equipment, touch something metallic such as a doorknob to remove static electricity from your body. Never touch the remote controller board or the adapter board.
5. Keep the wiring away from any other power source lines to avoid electric noise (external noise).
6. Select a flat surface, wherever possible, to mount the remote controller. To prevent deformation of the cases, do not overtighten the mounting screws.

## 1. Securing the remote controller lower case

Insert a bladed screwdriver into the concave (凹) in the remote controller lower case to remove the upper case assembly (two locations).

The remote controller board is located on the upper case. Take care not to scratch the board with the screwdriver.




### (1) Exposed mounting

Secure the remote controller lower case with the two supplied wood screws.



### (2) Embedded mounting


Secure the remote controller lower case with the two supplied machine screws.




For the field supplied switch box, use optional accessories KJB1111A or KJB2121A.

## 2. Securing the remote control adapter


Remove the upper case of the remote control adapter and secure the lower case assembly.



## 3. Wiring



## 4. Placing the upper case assembly of the remote controller and the upper case of the remote controller adapter back into their original positions



## 5. Temperature indication change

To change from Celsius temperature indication to Fahrenheit one

Press and hold down at the same time for 5 seconds while the Celsius temperature is indicated.



← See Operation Manual