


**DAIKIN**

---

# OPERATING MANUAL

---




Operating Manual  
Handset Wireless


**English**

OM-GS02-0211(0)-DAIKIN (SASO)  
Part No.: R08019036067


# GS02 Remote Control Indication




# HOW TO MOUNT ONTO THE WALL



# TO INSERT BATTERIES (AAA.R03)



# REMOTE CONTROLLER LOSS PREVENTION WITH BALL CHAIN (OPTIONAL)



## Installation

1. Match the ring at the end of the ball chain with the screw hole on the back of the remote controller and secure it with the screw.
2. Attach the holder and the ball chain as above at the position where signals from the remote controller can be received easily.
3. Pass the ball chain through the back of the holder and match the ring at the end of the ball chain to the upper hole of the holder. Fix the holder to the wall by putting through 2 screws across it.

## 1. Transmission source

- The source where the signal will be transmitted.


## 2. Signal transmission indication

- Blink to confirm that the last setting has been transmitted to the unit.

## 3. “ON/OFF” Button

- Press once to start the air conditioner unit.
- Press again to stop the unit.

## 4. Fan speed selection

- Pressing the  button continuously will toggle the fan speed in the following order:



Low → Med → High → Auto

- Stop pressing when the desired fan speed appears on the display screen.






## 5. Operation mode

- Press the **MODE** button to select the type of operating mode.
- For cooling only unit, the available modes are: **COOL** (\*), **DRY** (💧) and **FAN** (🌀).
- For heat pump unit, the available modes are: **AUTO** (△), **COOL** (\*), **DRY** (💧), **FAN** (🌀) and **HEAT** (☀️).
- The **AUTO** (△) mode is unavailable for chilled water system.

## 6. Automatic air swing

- Press the **SWING**  button to activate the automatic air swing function.
- To distribute the air to a specific direction, press the **SWING**  button and wait until the louver move to the desired direction and press the button once again.


### Swing mode selection method (for CK-E model)

- Press **SWING** () button for 4 seconds to enter field setting mode. While in field setting mode, it will only show **SWING MODE** ()
- Press temperature  and  button to select **SWING MODE** () rotation from Swing Mode 1 to Swing Mode 3.
- There are 3 different **SWING MODE**, which are:




     
      
   
 Swing mode 1      Swing mode 2      Swing mode 3

**SWING MODE** will not activate unless **SWING** is activated.

Swing is indicated by the logo: 

- If no mode changes within 4 seconds, unit will operate according to the selected **SWING MODE** ()

## 7. Turbo function (model dependent)

- Press  for fast cooling or heating operation.
- Fan speed turn to maximum speed.
- Press again to deactivate the function.
- Available under **HEAT** and **COOL** modes only.
- Any change of fan speed will deactivate this function.
- The Turbo function () is unavailable for chilled water system and remote control with **SWING MODE** () function.

## 8. OFF timer setting

- Press the **OFF TIMER** button will activate the off timer function.
- Set the desired off time by pressing the **OFF TIMER** button continuously.
- Press the **CANCEL** button to cancel the off timer setting.

## 9. Quiet function (model dependant)

- Press  $\text{Ⓢ}$  for quiet operation.
- Fan speed turn to minimum speed.
- Press again to deactivate the function.
- Any change of fan speed will deactivate this function.
- The Silent function ( $\text{Ⓢ}$ ) is unavailable for chilled water system.

## 10. Clock time setting


- Press and hold  $\text{⌚}$  button to set the clock time.

## 11. ON timer setting

- Press the **ON TIMER** button will activate the on timer function.
- Set the desired on time by pressing the **ON TIMER** button continuously. If the timer is set to 7.30am, the air conditioner will turn on at 7.30am sharp.
- Press the **CANCEL** button to cancel the on timer setting.

## 12. Sleep mode setting

- Press the  $\text{★}$  button will activate the sleep mode function.
- This is an energy saving option. When the unit is operating under cooling mode, the set temperature is increased by  $0.5^{\circ}\text{C}$  after the first half an hour, another  $0.5^{\circ}\text{C}$  after the second half an hour and  $1^{\circ}\text{C}$  after the following 1 hour.
- When the unit is operating under heating mode, the set temperature is decreased by  $1^{\circ}\text{C}$  after the first half an hour, another  $1^{\circ}\text{C}$  after the second half an hour and  $1^{\circ}\text{C}$  after the following 1 hour.
- This function is available under **COOL**, **HEAT** and **AUTO** mode.



## 13. Temperature setting

- To set the desired room temperature, press the  $\blacktriangle$  or  $\blacktriangledown$  button to increase or decrease the set temperature.
- The temperature setting range is from  $16^{\circ}\text{C}$  to  $30^{\circ}\text{C}$  (Optional setting  $20^{\circ}\text{C}$  to  $30^{\circ}\text{C}$ ).
- Press both buttons  $\blacktriangle$  and  $\blacktriangledown$  simultaneously to toggle from  $^{\circ}\text{C}$  to  $^{\circ}\text{F}$  setting.

# MEMO