

Wall mounted unit

FXAQ-P



Whisper quiet



Vertical auto swing



Multi tenant

For rooms with no false ceilings nor free floor space

- › Flat, stylish front panel blends easily within any interior décor and is more easy to clean
- › Can easily be installed in both new and refurbishment projects
- › 15 class unit especially developed for small or well-insulated rooms, such as hotel bedrooms, small offices, etc.
- › The air is comfortably spread up and downwards thanks to 5 different discharge angles that can be programmed via the remote control


FXAQ-P



Indoor unit		FXAQ	15P	20P	25P	32P	40P	50P	63P	
Cooling capacity	Nom.	kW	1.7	2.2	2.8	3.6	4.5	5.6	7.1	
Heating capacity	Nom.	kW	1.9	2.5	3.2	4.0	5.0	6.3	8.0	
Power input - 50Hz	Cooling	Nom.	kW	0.017	0.019	0.028	0.030	0.020	0.033	0.050
	Heating	Nom.	kW	0.025	0.029	0.034	0.035	0.020	0.039	0.060
Dimensions	Unit	Height	mm	290						
		Width	mm	795			1,050			
		Depth	mm	238			14			
Weight	Unit	kg	11			14				
Casing	Colour		White (3.0Y8.5/0.5)							
Fan-Air flow rate - 50Hz	Cooling	High/Low	m ³ /min	7.0/4.5	7.5/4.5	8/5	8.5/5.5	12/9	15/12	19/14
Air filter	Type			Washable resin net						
Sound power level	Cooling	Nom.	dBA	-						
Sound pressure level	Cooling	High/Low	dBA	34.0/29.0	35.0/29.0	36.0/29.0	37.5/29.0	39.0/34.0	42.0/36.0	47.0/39.0
		Refrigerant	Type/ GWP		R-410A/ 2.087,5					
Piping connections	Liquid	OD	mm	6.35						9.52
	Gas	OD	mm	12.7						15.9
	Drain			VP13 (I.D. 13/O.D. 18)						
Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/220-240							
Current - 50Hz	Maximum fuse amps (MFA)	A	16							
Control systems	Infrared remote control		BRC7EB518							
	Simplified wired remote control for hotel applications		-							
	Wired remote control		BRC1E52A/B / BRC1D52							

Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-245

02/15



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.