

Air conditioners

Heating & Cooling



- » Easy control at your fingertips
- » Turbo mode
- » Anti-corrosion treated outdoor unit
- » Wide range, from 25 to 60 class



















timer





Heating & Cooling

Indoor unit				FTXV25A	FTXV35A	FTXV50A	FTXV60A	
Cooling capacity	Nom.	n.		2.60	3.60	5.30	5.65	
Heating capacity	Nom.		kW	2.65	3.84	5.50	6.18	
Nominal efficiency				3.25	3.30	3.25	3.23	
heating at 7°/20°	COP			3.63	3.62		3.64	
	Annual energy co	onsumption	kWh	400	545	815	875	
	Energy label	Cooling		A				
		Heating		A				
Dimensions	Unit	HeightxWidthxDepth	mm	265x790x170	275x845x180	298x940x200	315x1,007x219	
Weight	Unit		kg	9	11	12	14	
Fan-Air flow rate	Cooling	High/Nom./Low/Silent operation	m³/min	9.2/8.3/6.7/5	10/8.3/6.7/5	14.2/13/10.8/9.2	15/13.3/11.7/9.2	
Sound pressure level	Cooling	High/Nom./Low/Silent operation	dBA	40/37/35/32	42/39/36/33	48/46/40/35	51/47/42/39	
Piping connections	Liquid	quid OD		6				
	Gas OD		mm	9.52		12.7	15.9	
Power supply	ver supply Phase / Frequency / Voltage Hz / V			1~/50/220-240				

Outdoor unit					RXV25A	RXV35A	RXV50A	RXV60A	
Dimensions	Unit	HeightxWic	dthxDepth	mm	540x776x320		596x899x378	700x955x396	
Weight	Unit	it kg			31	32	38	48	
Compressor	Туре				Rotary				
Sound pressure level	Cooling	Nom.		dBA	50	52	54		
Operation range	Cooling	Ambient	Min.~Max.	°CDB	18~43				
	Heating	Ambient	Min.~Max.	°CWB	-7~24				
_	Туре				R-410A				
	GWP				1,975				
connections	Liquid	OD		mm	6				
	Gas	OD		mm	9.52		12.7	15.9	
	Piping length	OU - IU	Max.	m	15		20		
	Level difference	IU - OU	Max.	m		1	0		
Power supply	Phase / Frequency / Voltage Hz / V 1~/50/220-240								







Infrared remote control



Outdoor unit RXV-A

Daikin has a worldwide reputation based on 90 years' experience in the successful manufacture of high quality air conditioning equipment for residential, commercial and industrial use and 56 years as a leader in heat pump technology.

Daikin products are distributed by:

Daikin products are distributed by:

Daikin products are distributed by:

Daikin Europe NV. Daikin Europe NV. Daikin Europe NV. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability of firest for particular propose of its content of this leaflet to the use and/or interpretation of this leaflet. All contents to content is copyrighted by Daikin Europe NV.

Daikin Europe N.V. Naamloze Vennootschap - Zandvoordestraat 300, B-8400 Oostende - Belgium - www.daikin.eu - BE 0412 120 336 - RPR Oostende Daikin has a worldwide reputation based on 90 years' experience in the successful manufacture of high quality



