

Ceiling suspended unit

FXHQ-A



For wide rooms with no false ceilings nor free floor space

- › Ideal for comfortable air flow in wide rooms thanks to Coanda effect: up to 100° discharge angle
- › Even rooms with ceilings up to 3.8m can be heated up or cooled down very easily without capacity loss
- › Can easily be installed in both new and refurbishment projects
- › Can easily be mounted in corners and narrow spaces, as it only needs 30mm lateral service space
- › Reduced energy consumption thanks to specially developed DC fan motor and drain pump


FXHQ-A



Indoor unit		FXHQ	32A	63A	100A	
Cooling capacity	Nom.	kW	3.6	7.1	11.2	
Heating capacity	Nom.	kW	4.0	8.0	12.5	
Power input - 50Hz	Cooling	Nom.	0.107	0.111	0.237	
	Heating	Nom.	0.107	0.111	0.237	
Dimensions	Unit	Height	mm			
		Width	960	1,270	1,590	
		Depth	mm			
Weight	Unit	kg	24	33	39	
Casing	Colour	Fresh White				
	Material	Resin				
Fan-Air flow rate - 50Hz	Cooling	High/Nom./Low	m ³ /min	14.0/12.0/10.0	20.0/17.0/14.0	29.5/24.0/19.0
	Heating	High/Nom./Low	m ³ /min	14.0/12.0/10.0	20.0/17.0/14.0	29.5/24.0/19.0
Air filter	Type	Resin net with mold resistance				
Sound power level	Cooling	Nom.	dBA			
Sound pressure level	Cooling	High/Nom./Low	dBA			
	Heating	High/Nom./Low	dBA			
Refrigerant	Type/ GWP	R-410A / 2.087,5				
Piping connections	Liquid	OD	mm	6.35	9.52	
	Gas	OD	mm	12.7	15.9	
	Drain	VP20 (I.D. 20/O.D. 26)				
Power supply	Phase/Frequency/Voltage	Hz/V				
Current - 50Hz	Maximum fuse amps (MFA)	A				
Control systems	Infrared remote control	BRC7G53				
	Simplified wired remote control for hotel applications	-				
	Wired remote control	BRC1E52A/B / BRC1D52				

Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-246

02/15



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.