



Air conditioners

# Heating & Cooling

*Siesta*

- » Stylish front panel
- » Silent operation
- » Vertical auto swing
- » Standard air filter
- » Anti-corrosion treated outdoor heat exchanger fin
- » SEER/SCOP:  
Up to **A<sup>+</sup>**


Wall mounted unit



[www.daikin.eu](http://www.daikin.eu)



ATXN-MB



Self diagnosis

# Heating & Cooling



INDOOR UNIT			ATXN25MB	ATXN35MB	ATXN50MB	ATXN60MB	
Cooling capacity	Min./Nom./Max.		kW				
			1.30/2.56/3.00	1.30/3.41/3.80	1.63/5.48/6.20	1.75/6.23/6.50	
Heating capacity	Min./Nom./Max.		kW				
			1.30/2.84/4.00	1.30/3.58/4.75	1.17/5.62/6.60	1.20/6.40/7.10	
Power input	Cooling	Nom.	kW				
			0.693	1.205	1.718	1.931	
	Heating	Nom.	kW				
			0.700	0.950	1.500	1.680	
Seasonal efficiency (according to EN14825)	Cooling	Energy label		A+			
		Pdesign	kW	2.56	3.41	5.48	6.23
		SEER			5.61		5.15
		Annual energy consumption	kWh	160	213	342	423
	Heating (Average climate)	Energy label		A			
		Pdesign	kW	2.51	2.58	3.64	3.80
		SCOP		3.81		3.99	3.81
		Annual energy consumption	kWh	922	948	1,277	1,396
Casing	Colour		White				
Dimensions	Unit	HeightxWidthxDepth	mm				
			288x800x206			310x1,065x224	
Weight	Unit			kg			
				9		14	
Fan-Air flow rate	Cooling	Super high/High/Nom./Low/Silent operation	m <sup>3</sup> /min				
			10.68/9.78/7.68/6.06/4.68	11.10/10.14/7.98/6.54/4.68	16.38/15.00/13.32/11.82/10.62	19.92/18.54/16.56/14.34/12.36	
	Heating	Super high/High/Nom./Low/Silent operation	m <sup>3</sup> /min				
			10.68/9.78/7.68/6.06/4.68	11.10/10.14/7.98/6.54/4.68	16.38/15.00/13.32/11.82/10.62	19.92/18.54/16.56/14.34/12.36	
Sound power level	Cooling			dBA			
				53		54	
Sound pressure level	Cooling	Super high/High/Nom./Low/Silent operation	dBA				
			41/40/34/29/21	42/41/34/30/22	44/40/38/35/32	46/43/41/37/33	
Power supply	Phase / Frequency / Voltage		Hz / V				
			1~ / 50 / 220-240				

OUTDOOR UNIT			ARXN25MB	ARXN35MB	ARXN50MB	ARXN60MB
Dimensions	Unit	HeightxWidthxDepth	mm			
			550x658x289			753x855x328
Weight	Unit			kg		
				31		44
Compressor	Type		Hermetic swing			
Sound power level	Cooling			dBA		
				58		60
Sound pressure level	Cooling	Nom.	dBA			
			45	46	64	51
Operation range	Cooling	Ambient	Min.~Max.		°CDB	
					10~46	
	Heating	Ambient	Min.~Max.		°CWB	
					-10~46	
Refrigerant	Type		R-410A			
	GWP		1,975			
Piping connections	Liquid	OD	mm		6.35	
	Gas	OD	mm		9.52	
	Piping length	OU-IU	Max.	m		20
Power supply	Phase / Frequency / Voltage		Hz / V			
			1~ / 50 / 220-240			



ATXN25-35MB



AP GS02



ARXN25-35MB

Daikin has a worldwide reputation based on 90 years' experience in the successful manufacture of high quality air conditioning equipment for residential, commercial and industrial use and 56 years as a leader in heat pump technology.

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU) and Fan coil units (FCU). Check ongoing validity of certificate online: [www.eurovent-certification.com](http://www.eurovent-certification.com) or using: [www.certiflash.com](http://www.certiflash.com)

Printed on non-chlorinated paper. Prepared by La Mevrida, Belgium.  
Resp. Ed.: Daikin Europe N.V., Zandvoordestraat 300, B-8400 Oostende

Daikin products are distributed by:

FSC

ECPEN14-032