



Concealed ceiling unit

ADEQ-C


Siesta



Ideal for residential applications with false ceilings

- › Energy efficient units: up to class A energy labels
- › Medium external static pressure up to 150Pa facilitates using flexible ducts of varying lengths
- › Slim indoor unit (300mm built-in height) suited for narrow ceiling installation
- › Exclusively offered for pair applications
- › Discretely concealed in the ceiling; only the suction and discharge grilles are visible

ADEQ-C + ARXS-L/AZQS-B8V1/ ARXS-L3



Indoor unit		ADEQ	35C	50C	60C	71C	100C	125C
Casing	Colour		Unpainted					
Dimensions	Unit	HeightxWidthxDepth	mm	245x700x800		245x1,000x800		245x1,400x800
Sound power level	Cooling		dB	60		56		62
Sound pressure level	Cooling	High/Nom./Low	dB	35/35/29		30/30/25		37/37/32
	Heating	High/Nom./Low	dB	37/37/29		31/31/25		38/38/32


Efficiency data		ADEQ	35C + ARXS35L3	50C + ARXS50L	60C + ARXS60L	71C + ARXS71L	71C + AZQS71BV1	100C + AZQS100B8V1	125C + AZQS125B8V1	
Cooling capacity	Nom.	kW	3.40	5.00	5.70	6.80		9.50	12.1	
Heating capacity	Nom.	kW	4.00	5.50	7.00	7.50		10.8	13.5	
Power input	Cooling	Nom.	kW	0.920	1.56	1.70	2.55	2.12	2.96	3.89
	Heating	Nom.	kW	1.01	1.48	1.94	2.16	2.08	2.99	3.91
Seasonal efficiency (according to EN14825)	Cooling	Energy efficiency class		A+			A			-
		Pdesign	kW	3.40	5.00	5.70	6.80		9.50	-
		SEER		5.70	5.60	5.70	5.30	5.40	5.10	-
	Heating (Average climate)	Annual energy consumption	kWh	209	313	350	449	441	652	-
		Energy efficiency class		A+			A			-
		Pdesign	kW	2.90	4.40	4.60	6.00		7.60	-
Nominal efficiency	Annual energy consumption	SCOP/A		4.00		3.80		3.81	-	
		Annual energy consumption	kWh	1,015	1,540	1,610	2,210	2,205	2,793	-
		EER		-						
	COP		-							
	Annual energy consumption	kWh	-							

Contains fluorinated greenhouse gases

Outdoor unit		ARXS35L3	ARXS50L	ARXS60L	ARXS71L	AZQS71BV1	AZQS100B8V1	AZQS125B8V1		
Dimensions	Unit	HeightxWidthxDepth	mm	550x765x285	735x825x300		770x900x320	990x940x320		
Sound power level	Cooling		dB	61	62	65	64	70	71	
	Heating		dB	61	62	65		-		
Sound pressure level	Cooling	High/Nom./Low/Silent operation	dB	48/-/44/-	48/-/44	-/49/-/-	-/52/-/-	-/48/-/-	-/53/-/-	-/54/-/-
	Heating	High/Nom./Low/Silent operation	dB	48/-/45/-	48/-/45	-/49/-/-	-/52/-/-	-/50/-/-	-/57/-/-	-/58/-/-
	Night quiet mode	Level 1	dB	-			43	49		
Operation range	Cooling	Ambient	Min.-Max.	°CDB	10~46		-10~46		-5~46	
	Heating	Ambient	Min.-Max.	°CWB	-15~18				-15~15.5	
Refrigerant	Type/Charge/GWP	kg/TCO ₂ eq		R-410A/1.2/2.5/2,0875	R-410A/1.7/3.5/2,0875	R-410A/1.50/-/2,0875	R-410A/1.70/-/2,0875	R-410A/2.75/5.7/2,0875	R-410A/2.9/6.1/2,0875	
Power supply	Phase/Frequency/Voltage	Hz/V		1~/50/220-240		1~/50/220-230-240		1~/50/220-240		

Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU), Fan coil units (FCU) and variable refrigerant flow systems (VRF) Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com

ECPEN17-134_1

02/17



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.