

# Wall mounted unit

ATXF-A / ATXF-D + ARXF-A / ARXF-D

*Siesta*

DAIKIN



Fan speed steps



Econo mode



Energy saving during standby mode



Fan only



Comfort mode

Siesta wall mounted unit for low energy consumption and pleasant comfort

- › Designed to combine with multi outdoor units only
- › Daikin residential controller via app (optional)
- › Onecta (optional)
- › Voice control
- › Quiet in operation
- › Bluevolution range: lower environmental impact

# ATXF-A / ATXF-D + ARXF-A / ARXF-D



Efficiency data		ATXF + ARXF	20D + 20D	25D + 25D	35D + 35D	42D + 42D	50A + 50A	60A + 60A	71A + 71A			
Cooling capacity	Min./Nom./Max.	kW	1.3 /2.00 /2.4	1.3 /2.50 /2.8	1.3 /3.30 /3.8	1.4 /4.20 /4.3	1.70 /5.00 /6.00	1.70 /6.00 /7.00	2.30 /7.10 /7.30			
Heating capacity	Min./Nom./Max.	kW	1.30 /2.40 /3.30	1.30 /2.80 /3.70	1.30 /3.50 /4.40	1.40 /4.60 /5.00	1.70 /6.00 /7.70	1.70 /6.40 /8.00	2.30 /8.20 /9.00			
Power input	Cooling	Min./Nom./Max.	kW	0.31 /0.601 /0.72	0.31 /0.772 /1.05	0.31 /1.01 /1.40	0.31 /1.28 /1.50	-/1.52 /-	-/1.85 /-	-/2.81 /-		
	Heating	Min./Nom./Max.	kW	0.25 /0.640 /0.95	0.25 /0.751 /1.11	0.25 /0.940 /1.50	0.25 /1.24 /1.40	-/1.62 /-	-/1.64 /-	-/2.63 /-		
Space cooling	Energy efficiency class		A++						A			
	Capacity	Pdesign	kW	2.00	2.50	3.50	4.20	5.00	6.00	7.10		
	SEER			6.40						6.18	6.12	5.12
	Annual energy consumption		kWh/a	109	137	191	228	283	343	486		
Space heating (Average climate)	Energy efficiency class		A+						A			
	Capacity	Pdesign	kW	2.20	2.40	2.60	3.30	4.60	4.80	6.20		
	SCOP/A			4.01						4.03		3.81
	Annual energy consumption		kWh/a	757	837	907	1,086	1,598	1,670	2,278		


Nominal cooling capacities are based on: indoor temperature: 27°CDB, 19°CWB, outdoor temperature: 35°CDB, equivalent refrigerant piping: 5m, level difference: 0m. Data for high efficiency series, Eurovent certified | Nominal heating capacities are based on: indoor temperature: 20°CDB, outdoor temperature: 7°CDB, 6°CWB, equivalent refrigerant piping: 5m, level difference: 0m. Data for standard efficiency series

Indoor unit		ATXF/ATXF	20D	25D	35D	42D	50A	60A	71A			
Dimensions	Unit	HeightxWidthxDPTH	mm				286 x770 x225			295 x990 x263		
Weight	Unit		8.00		8.50		9.00		13.5			
Air filter	Type		Removable / washable									
Fan	Air flow rate	Cooling	Silent operation/ Low/Medium/ High	m³/min	4.3 /6.0 /8 /9.8	4.3 /6.2 /8 /10.0	4.4 /6.4 /8 /11.5	4.9 /6.9 /9 /12.6	10.5 /11.9 /14.4 /16.8	10.7 /12.2 /14.8 /17.3		
		Heating	Silent operation/ Low/Medium/ High	m³/min	5.3 /6.2 /8.3 /10.4	5.3 /6.4 /8.4 /10.4	5.3 /6.5 /8.6 /11.9	5.2 /6.7 /8.8 /12.8	10.7 /12.2 /14.8 /17.3	11.3 /12.8 /15.8 /17.9		
Sound power level	Cooling		dB(A)	53.0		54.0		59.0		59	60	62
	Heating		dB(A)	55.0		56.0		59.0		61		62
Sound pressure level	Cooling	Silent operation/Low/High	dB(A)	20.0 /25.0 /39.0	20.0 /26.0 /40.0	20.0 /27.0 /43.0	22.0 /30.0 /45.0	31 /34 /43	33 /36 /45	34 /37 /46		
	Heating	Silent operation/Low/High	dB(A)	21.0 /28.0 /39.0	21.0 /28.0 /40.0	21.0 /29.0 /40.0	22.0 /28.0 /44.0	30 /33 /42	32 /35 /44	33 /36 /45		
Control systems	Infrared remote control		ARC470A1									
	Wired remote control		BRC073A1									
Piping connections	Drain		18									

Cooling: indoor temp. 27°CDB, 19°CWB; outdoor temp. 35°CDB; equivalent piping length: 5m; level difference: 0m | Heating: indoor temp. 20°CDB; outdoor temp. 7°CDB, 6°CWB; equivalent refrigerant piping: 5m (horizontal) | See separate drawing for electrical data

Outdoor unit		ARXF/ARXF	20D	25D	35D	42D	50A	60A	71A		
Dimensions	Unit	HeightxWidthxDPTH	mm				550 x658 x275			734 x870 x373	
Weight	Unit		24.0		28.0		46.0		50.0		
Sound power level	Cooling		-								
Sound pressure level	Cooling	Low/Nom./High	dB(A)	-/ /46.0		-/ /48.0		-/47 /-		-/49 /-	-/52 /-
	Heating	Low/Nom./High	dB(A)	-/ /47.0		-/ /48.0		-/49 /-		-/52 /-	
Operation range	Cooling	Ambient	Min.~Max.	°CDB				-10 ~48			
	Heating	Ambient	Min.~Max.	°CWB				-15 ~18			
Refrigerant	Type		R-32								
	GWP		675.0								
	Charge	kg/TCO2Eq	0.450 /0.300	0.550 /0.370	0.750 /0.510	0.90 /0.61	1.15 /0.78				

Daikin Europe Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · <https://www.daikin.eu> · · RPR Oostende (Responsible Editor)



Daikin Europe N.V. participates in the ECP programmes for Fan Coil Units and Variable Refrigerant Flow systems. Daikin Applied Europe S.p.A. participates in the ECP programmes for Liquid Chilling Packages and Hydronic Heat Pumps. Check ongoing validity of certificate: [www.eurovent-certification.com](http://www.eurovent-certification.com)

ECPEN22-061

01/2022



The present publication is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. / Daikin Central Europe HandelsGmbH. Daikin Europe N.V. / Daikin Central Europe HandelsGmbH have compiled the content of this publication to the best of their knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. / Daikin Central Europe HandelsGmbH explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this publication. All content is copyrighted by Daikin Europe N.V.