

Air Conditioners

Heating & Cooling



- » As silent as rustling leaves
- » Draught-free
- » Vertical auto swing
- » Special air filter improves indoor air quality
- » SEER:A+





ATX-JV

Heating & Cooling





INDOOR UNIT				ATX20JV	ATX25JV	ATX35JV	
Cooling capacity	Min./Nom./Max.		kW	1.3/2.0 /2.6	1.3/2.5 /3.0	1.3/3.3 /3.8	
Heating capacity	Min./Nom./Max.		kW	1.3/2.5 /3.5	1.3/2.8 /4.0	1.3/3.5 /4.8	
efficiency (according to EN14825)	Cooling	Energy label		A+			
		Pdesign	kW	2.00	2.50	3.30	
		SEER		5.63	5.63	5.66	
		Annual energy consumption	kWh	124	155	204	
	Heating (Average climate)	Energy label		A++	A+		
		Pdesign	kW	2.20	2.40	2.80	
		SCOP		4.67	4.50	4.14	
		Annual energy consumption	kWh	660	747	945	
hosting at 7°/20°	EER			3.64	3.42	3.37	
	COP			4.24	4.06	3.76	
	Annual energy of	consumption	kWh	275	365	490	
	Energy label	Cooling		A			
		Heating		A			
Casing	Colour			White			
Dimensions	Unit	HeightxWidthxDepth	mm	283x770x198			
Weight	Unit		kg	7			
Fan - Air flow rate	Cooling	High/Nom./Low/Silent operation	m³/min	9.1/9.1/5.9/4.7	9.2/9.2/6.0/4.8	9.3/9.3/6.1/4.9	
	Heating	High/Nom./Low/Silent operation	m³/min	9.4/7.8/6.3/5.5	9.7/8.0/6.3/5.5	10.1/8.4/6.7/5.7	
Sound power level	Cooling	Nom.	dBA	55	55	58	
	Heating	Nom.	dBA	55	56	57	
1	Cooling	High/Nom./Low/Silent operation	dBA	39/33/25/22	40/33/26/22	41/34/27/23	
	Heating	High/Nom./Low/Silent operation	dBA	39/34/28/25	40/34/28/25	41/35/29/26	
Piping connections	Liquid OD		mm	6.35			
	Gas OD		mm	9.52			
	Drain OD		mm	18.0			
Power supply	Phase / Frequen	cy / Voltage	Hz/V	1~/50/220-230-240			

(1) EER/COP according to Eurovent 2012

OUTDOOR UNIT					ARX20JV	ARX25JV	ARX35JV	
Dimensions	Unit HeightxWidthxDepth			mm	550x658x275			
Weight	Jnit .			kg	28	28	30	
Sound power level	Cooling	Nom.		dBA	60	60	62	
Sound pressure level	Cooling	High		dBA	46	46	48	
	Heating	High		dBA	47	47	48	
Compressor	Type				Hermetically sealed swing compressor			
Operation range	Cooling	Ambient	Min.~Max.	°CDB	10~46			
	Heating	Ambient	Min.~Max.	°CWB	-15~20			
Refrigerant	Туре				R-410A			
	GWP				1,975			
Piping connections	Liquid	OD		mm	6.35			
	Gas	OD		mm	9.52			
	Drain	OD		mm	18.0			
	Piping length	OU - IU	Max.	m	15			
	Level difference	IU - OU	Max.	m	12			
Power supply	Phase / Frequency / Voltage			Hz/V	1~/50/220-230-240			







ATX-JV

REMOTE CONTROL

ARX-JV



Daikin's unique position as a manufacturer of air conditioning equipment, compressors and refrigerants has led to its close involvement in environmental issues. For several years Daikin has had the intention to become a leader in the provision of products that have limited impact on the environment. This challenge demands the eco design and development of a wide range of products and an energy management system, resulting in energy conservation and a reduction of waste.









Daikin Europe N.V. participates in the Eurovent Certification programme for Air conditioners (AC), Liquid Chilling Packages (LCP) and Fan coil units (FCU), Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com

FSC

ECPEN13-031A

Daikin products are distributed by:

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe NV. Daikin Europe NV. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe NV. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe NV.