

Wall mounted unit

ATX-K



Siesta



Energy saving during standby mode



Online controller via app



Multi model application

Discreet Siesta wall mounted unit providing high efficiency and comfort

- › SEER / SCOP up to A++
- › Discreet, stylish front panel blends easily with the wall, and matches all interior décors
- › Whisper quiet in operation: the operating of the unit can hardly be heard. The sound pressure level goes down to 19dBA!

- › Online controller (optional): control your indoor from any location with an app, via your local network or internet
- › Dry programme allows humidity levels to be reduced without variations in room temperature

ATX-K + ARX-K



Indoor unit		ATX	20K	25K	35K
Casing	Colour		White		
Dimensions	Unit	HeightxWidthxDepth	mm		
			286x770x225		
Sound power level	Cooling/Heating		55/55		58/58
Sound pressure level	Cooling	High/Nom./Low/Silent operation	39/33/25/20	40/33/26/20	43/34/27/20
	Heating	High/Nom./Low/Silent operation	39/34/28/23	40/34/28/23	43/35/29/26
Control systems	Infrared remote control		ARC480A11		
	Wired remote control		BRC944B2 / BRC073		

Efficiency data		ATX + ARX	20K + 20K	25K + 25K	35K + 35K	
Cooling capacity	Min./Nom./Max.	kW	1.3/2.0/2.6	1.3/2.5/3.0	1.3/3.5/4.0	
Heating capacity	Min./Nom./Max.	kW	1.3/2.5/3.5	1.3/3.0/4.0	1.3/4.0/4.8	
Power input	Cooling	Min./Nom./Max.	0.310/0.504/0.720	0.310/0.661/0.720	0.290/1.020/1.300	
	Heating	Min./Nom./Max.	0.250/0.524/0.950	0.250/0.688/0.950	0.290/0.995/1.290	
Seasonal efficiency (according to EN14825)	Cooling	Energy label		A++		
		Pdesign	kW	2.00	2.50	3.50
		SEER		6.62	6.46	6.40
	Heating (Average climate)	Annual energy consumption	kWh	106	135	181
		Energy label			A++	
		Pdesign	kW	2.20	2.40	2.80
Nominal efficiency	EER		3.97	3.78	3.43	
		COP		4.77	4.36	4.02
	Annual energy consumption	kWh	252	331	510	
	Energy label	Cooling/Heating		A/A		

Outdoor unit		ARX	20K	25K	35K
Dimensions	Unit	HeightxWidthxDepth	mm		
			550x658x275		
Sound power level	Cooling		60		62
	Heating		61		62
Sound pressure level	Cooling	High	46		48
	Heating	High	47		48
Operation range	Cooling	Ambient	Min.-Max.	°CDB	
				-10~46	
Refrigerant	Heating	Ambient	Min.-Max.	°CWB	
				-15~18	
Type/GWP			R-410A/2,087.5		
	Charge		0.74/1.5	1.0/2.1	
Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/220-240		

EER/COP according to Eurovent 2012, for use outside EU only | Nominal efficiency: cooling at 35°/27° nominal load, heating at 7°/20° nominal load

Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-037

03/15



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU), Fan coil units (FCU) and variable refrigerant flow systems (VRF) Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.