


Daikin air conditioners
for your home

WALL MOUNTED UNIT



www.daikin.eu

FTXG/CTXG-E






The UX1 has already won the 'Good Design Award 2004' for its modern design. This stylish wall mounted unit is available in 2 colour variations: mat crystal white or mat crystal silver.

The UX1 not only breaks new ground technologically, it also adds a new dimension of comfort to your life in a very distinctive, stylish way.


COMFORT

- The **comfort mode** function ensures draught-free operation. During cooling operation the flap angle turns horizontally to prevent cold air blowing directly on to you. During heating operation it turns downward vertically to send the warm air direct to your feet.

Cooling mode



Heating mode



- The **3D air flow** function combines the vertical and horizontal auto swing to circulate a stream of cool/warm air right to the corners of even large spaces.



- The **indoor/outdoor unit silent operation** function increases comfort by offering industry leading quiet operation of 22dB(A) for the indoor unit and 43dB(A) for the outdoor unit.
- You have the choice of **5 fan speeds** to select: from high to super low.
- Daikin's special **dry programme** reduces humidity in the room without variations in room temperature.
- The **powerful operation function** boosts the air flow to a maximum volume for a 20-minute period, (e.g. when you come home on a hot day, rapid cooling is required). After this, the unit returns automatically to its previous settings.
- The **night set mode** is automatically selected by pushing the 'off' timer button. This function prevents any sudden change in room temperature by gently raising/lowering the temperature before the air conditioner stops, so you can sleep more comfortably.

Capacity and power input

HEAT PUMP-INVERTER CONTROLLED (air cooled)				FTXG25E-W/S	FTXG35E-W/S	CTXG50E-W/S
Cooling capacity		min~nom~max	kW	1.30~2.50~3.00	1.40~3.50~3.80	For more detailed information about capacities, power input, EER/COP, Energy label and Annual energy consumption, please refer to our Multi Model catalogue/combination tables / Super Multi Plus catalogue or check with your local dealer.
Heating capacity		min~nom~max	kW	1.30~3.40~4.50	1.40~4.20~5.00	
Nominal input	cooling	min~nom~max	kW	0.30~0.62~0.95	0.30~1.06~1.29	
	heating	min~nom~max	kW	0.29~0.82~1.42	0.31~1.13~1.56	
EER				4.03	3.30	
COP				4.15	3.72	
Energy label	cooling			A	A	
	heating			A	A	
Annual energy consumption			kWh	310	530	

1) Energy label: scale from A (most efficient) to G (less efficient)

2) Annual energy consumption: based on average use of 500 running hours per year at full load (=nominal conditions)

POSSIBLE COMBINATIONS		2MXS40F*(1)	2MXS50F*(2)	3MXS52E*(3)	4MXS68F*(4)	4MXS80E*(5)	5MXS90E*(5)	RMXS112E*	RMXS140E*	RMXS160E*
Max. n° of indoor units		2	2	3	4	4	5	7	8	9
Heat pump	FTXG25E-W	●	●	●	●	●	●	●	●	●
	FTXG25E-S	●	●	●	●	●	●	●	●	●
	FTXG35E-W	●	●	●	●	●	●	●	●	●
	FTXG35E-S	●	●	●	●	●	●	●	●	●
	CTXG50E-W			●	●	●	●	●	●	●
	CTXG50E-S			●	●	●	●	●	●	●
Max. cooling capacity	kW	4.50	5.40	7.30	8.73	9.60	10.50	4.50	5.40	15.5
Max. heating capacity	kW	4.70	6.40	8.30	10.68	11.00	11.50	12.5	16.0	17.5
Max. PI cooling	kW	1.35	1.70	2.25	2.95	3.56	4.01	3.50	5.09	5.40
Max PI heating	kW	1.18	1.65	2.51	2.58	3.11	3.46	3.93	5.21	5.43

Notes:

1) For more detailed information, please consult our multi model/combination tables catalogue or your local dealer

2) (1) The indicated cooling, heating capacities and power input are indicative and are those connected to wall mounted D,E (20,25,35 class) series

(2) The indicated cooling, heating capacities and power input are indicative and are those connected to wall mounted D,E (20,25,35,50 class) series

(3) The indicated cooling, heating capacities and power input are indicative and are those connected to wall mounted D (20,25,35 class) / E (50 class) series

(4) The indicated cooling, heating capacities and power input are indicative and are those connected to wall mounted D (20,25,35,50 class) / F (60,71 class) series

(5) The indicated cooling, heating capacities and power input are indicative and are those connected to wall mounted D (20,25,35,50 class) / E (60,71 class) series

3) N/A means not applicable since this unit is a cooling only unit

4) * At least two indoor units should be connected to these multi outdoor units

Specifications indoor units

INDOOR UNIT (air cooled)				FTXG25E-W/S	FTXG35E-W/S	CTXG50E-W/S
Dimensions		HxWxD	mm	275x840x150		
Weight			kg	9		
Front panel colour				Mat crystal white (W) / Mat crystal silver (S)		
Air flow rate	cooling	H/L/SL	m³/min	7.7/4.7/3.8	8.1/4.9/4.1	11.3/7.1/6.7
	heating	H/L/SL	m³/min	9.0/6.7/5.4	9.6/6.7/5.9	12.6/8.7/7.7
Fan speed				5 steps, silent and auto		
Sound pressure level	cooling	H/L/SL	dB(A)	38/25/22	39/26/23	47/35/32
	heating	H/L/SL	dB(A)	38/28/25	39/29/26	47/35/32
Sound power level	cooling	H	dB(A)	56	57	64
Piping connections	liquid		mm	ø6.4		
	gas		mm	ø 9.5		ø12.7
	drain		mm	ø18.0		
Heat insulation				Both liquid and gas pipes		

Indoor units: FTXG-E/CTXG-E



FTXG25,35E-W
CTXG50E-W



FTXG25,35E-S
CTXG50E-S

Specifications outdoor units

OUTDOOR UNIT				RXG25E	RXG35E
Dimensions	HxWxD		mm	550x765x285	
Weight			kg	32	
Casing colour				Ivory white	
Sound pressure level	cooling	H/L	dB(A)	46/43	47/44
	heating	H/L	dB(A)	47/44	48/45
Sound power level	cooling	H	dB(A)	61	62
Compressor				Hermetically sealed swing type	
Refrigerant type				R-410A	
Refrigerant charge			kg/m	0.02 (for piping length exceeding 10m)	
Maximum piping length			m	20	
Maximum level difference			m	15	
Operation range	cooling	from~to	°CDB	+10~46	
	heating	from~to	°CWB	-15~20	

Accessories: control systems

INDOOR UNITS	FTXG25E-W/S	FTXG35E-W/S	CTXG50E-W/S
Wiring adapter for time clock/remote control (1) (normal open / open pulse contact)		KRP413A1S	
Centralised control board up to 5 rooms (2)		KRC72	
Central remote control		DCS302CS1	
Unified ON/OFF control		DCS301B51	
Schedule timer		DST301B51	
Interface adapter (3)		KRP928A2S	

- 1) Wiring adapter is supplied by Daikin. Timer and other devices: field supply
- 2) Wiring adapter is also required for each indoor unit.
- 3) For DIII-NET adapter

Accessories: indoor units

INDOOR UNITS	FTXG25E-W/S	FTXG35E-W/S	CTXG50E-W/S
Titanium apatite photocatalytic air purification filter (with frame)		KAF952B41	
Titanium apatite photocatalytic air purification filter (without frame)		KAF952B42	
Anti-theft protection for remote control		KKF917AA4	

Accessories: outdoor units


OUTDOOR UNITS	RXG25E	RXG35E
Air direction adjustment grille		KPW937A4

Note:

- 1) V1 = 1~, 220-240V, 50Hz
- 2) Nominal cooling capacities are based on: indoor temperature 27°CDB/19°CWB • outdoor temperature 35°CDB • refrigerant piping length 7.5m • level difference 0m.
- 3) Nominal heating capacities are based on: indoor temperature 20°CDB • outdoor temperature 7°CDB/6°CWB • refrigerant piping length 7.5m • level difference 0m.
- 4) Capacities are net, including a deduction for cooling (an addition for heating) for indoor fan motor heat.
- 5) Units should be selected on nominal capacity. Max. capacity is limited to peak periods.
- 6) The sound pressure level is measured via a microphone at a certain distance from the unit (for measuring conditions; please refer to the technical databooks).
- 7) The sound power is an absolute value indicating the "power" which a sound source generates.


FILTER

- This wall mounted unit is equipped with a **titanium apatite photocatalytic air purification filter**. Micron scale fibres in this filter trap dust while the titanium apatite absorbs organic contaminants such as bacteria and viruses. In addition, the titanium oxide is activated by natural light, allowing it to break down and eliminate odours. The filter lasts for 3 years without replacement if washed about every 6 months.




FLEXIBLE INSTALLATION AND EASY TO USE AND MAINTAIN

- The outdoor unit can be installed on a roof or terrace or placed against an outside wall.
- Daikin remote controls give you **easy control at your fingertips**.
- Malfunction codes are shown on the digital display panel of the infrared remote control for **fast and easy maintenance**.
- Special anti-corrosion treatment of the outdoor unit's heat exchanger fin, gives **great resistance against acid rain and salt corrosion**. Additional resistance is provided by a rust proof steel sheet on the underside of the unit.



ENERGY EFFICIENT

- Energy label:** Class A
- Inverter technology:**
 - Improved energy efficiency: The use of integrated inverter control ensures maximum **energy efficiency** by supplying only the required heating or cooling load where a standard non inverter unit would supply maximum load in an on/off regime.




- Improved comfort: The rapid start up time provided by the inverter increases **comfort** by reducing the lead time in obtaining the required indoor temperature. Once the required temperature is reached, the inverter unit continuously scans the room for small changes and adjusts the room temperature in seconds, thereby increasing comfort once again.
- The **movement sensor** detects whether anyone is in the room. When the room is empty, the unit switches to economy mode and restarts when a person enters the room.

APPLICATION OPTIONS

- This model can be used for cooling only or heating.
- It is possible to use the indoor unit in pair (connecting one indoor to one outdoor) and multi applications (connecting up to 9 units in several rooms to 1 outdoor unit).



Infrared remote control (Standard)
ARC 433 A41



**In all of us,
a green heart**



Daikin's unique position as a manufacturer of air conditioning equipment, compressors and refrigerants has led to its close involvement in environmental issues. For several years Daikin has had the intention to become a leader in the provision of environmental friendly products. This challenge demands the eco design and development of a wide range of products and an energy management system; which involves energy conservation and reduction of waste.



Daikin Europe N.V. is approved by LRQA for its Quality Management System in accordance with the ISO9001 standard. ISO9001 pertains to quality assurance regarding design, development, manufacturing as well as to services related to the product.



ISO14001 assures an effective environmental management system in order to help protect human health and the environment from the potential impact of our activities, products and services and to assist in maintaining and improving the quality of the environment.



Daikin units comply with the European regulations that guarantee the safety of the product.



Daikin Europe NV participates in the Eurovent Certification Programme for Air Conditioners (AC), Liquid Chilling Packages (LCP) and Fan Coil Units (FC); the certified data of certified models are listed in the Eurovent Directory. Multi units are Eurovent certified for combinations up to 2 indoor units.

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V.. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.

Daikin products are distributed by:



DAIKIN EUROPE N.V.

Naamloze Vennootschap
Zandvoordstraat 300
B-8400 Ostend, Belgium
www.daikin.eu
BTW: BE 0412 120 336
RPR Oostende



EPLN07-003 / 500 / 03/07 / La Movidia
The present publication supersedes EPLE 06-13. Printed on non-chlorinated paper / Printed in Belgium
Copyright © Daikin