

Wall mounted unit

ATXL-JV



Siesta



Guaranteed operation down to -25°C



Comfort mode



Online controller via app

Siesta wall mounted unit providing high efficiency and comfort, even at ambient temperatures **down to -25°C**

- › The unit's compact dimensions makes it ideal for renovation projects, especially for above door installation
- › Excellent air flow and air distribution
- › Online controller (optional): control your indoor from any location with an app, via your local network or internet
- › Guaranteed heating capacity at low ambient temperature, down to -25°C
- › Thanks to the unique free hanging coil technology, the defrost cycle is improved, resulting in lower running costs and no ice buildup

ATXL-JV + ARXL-M



Indoor unit		ATXL	25JV	35JV
Casing	Colour		White	
Dimensions	Unit	HeightxWidthxDepth	mm	
			283x770x198	
Sound power level	Cooling/Heating		dBA	
			57/57	
Sound pressure level	Cooling	High/Nom./Low/Silent operation	dBA	
			41/34/27/23	
level	Heating	High/Nom./Low/Silent operation	dBA	
			41/35/29/26	
Control systems	Infrared remote control		ARC433A87	

Efficiency data		ATXL + ARXL	25JV + 25M	35JV + 35M
Cooling capacity	Min./Nom./Max.	kW	1.2/2.5/3.4	1.3/3.5/3.8
Heating capacity	Min./Nom./Max.	kW	1.1/3.2/5.5 / 3.14 (1)	1.2/3.8/6.0 / 3.54 (1)
Power input	Cooling	Min./Nom./Max.	kW	0.29/0.80/1.30
	Heating	Min./Nom./Max.	kW	0.24/0.72/2.14
Seasonal efficiency (according to EN14825)	Cooling	Energy label		A+
		Pdesign	kW	2.50
		SEER		6.01
	Heating (Average climate)	Energy label		A+
		Pdesign	kW	2.50
		SCOP		4.37
Nominal efficiency	EER		3.12	3.07
		COP	4.43	4.21
	Annual energy consumption	kWh	400.5	570
	Energy label	Cooling/Heating		B/A


Outdoor unit		ARXL	25M	35M
Dimensions	Unit	HeightxWidthxDepth	mm	
			550x858x330	
Sound power level	Cooling		dBA	
			61	
Sound pressure level	Heating		dBA	
			61	
Operation range	Cooling	High/Low	dBA	
			48/44	
Refrigerant	Heating	High/Low	dBA	
			49/45	
Charge	Cooling	Ambient	Min.-Max.	°CDB
				-10~46
Power supply	Heating	Ambient	Min.-Max.	°CWB
				-25~18
Refrigerant	Type/GWP		R-410A/2,087.5	
Charge	kg/TCO ₂ Eq		1/2.1	
Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/220-240	

EER/COP according to Eurovent 2012, for use outside EU only | Nominal efficiency: cooling at 35°/27° nominal load, heating at 7°/20° nominal load

(1) Maximum average heating capacity at -15°C

Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-034

02/15



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU) and Fan coil units (FCU). Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.