



Air conditioners

Heating & Cooling

FULL RANGE
A CLASS
ENERGY LABEL

- » **Stylish flat front panel**
- » **Indoor unit silent operation**
- » **Special air filter**
- » **Anti-corrosion treated outdoor heat exchanger fin**


Wall mounted unit



www.daikin.eu



FTXN-M



Heating & Cooling

INDOOR UNIT			FTXN25M	FTXN35M	FTXN50M	FTXN60M	
Cooling capacity	Min./Nom./Max.	kW	1.30/2.55/3.00	1.30/3.32/3.80	1.63/5.65/6.20	1.75/6.30/6.50	
Heating capacity	Min./Nom./Max.	kW	1.30/2.84/3.90	1.30/3.58/4.75	1.17/5.62/6.60	1.25/6.40/7.10	
Power input	Cooling	Nom.	0.73	0.97	1.65	1.88	
	Heating	Nom.	0.70	0.95	1.50	1.68	
Nominal efficiency (cooling at 35°/27° nominal load, heating at 7°/20° nominal load)	EER		3.49		3.42	3.35	
	COP		4.06	3.77	3.75	3.81	
Annual energy consumption		kWh	365	485	825	940	
Energy label	Cooling				A		
	Heating				A		
Casing	Colour		White				
Dimensions	Unit	HeightxWidthxDepth	288x800x206		310x1,065x224		
Weight	Unit		9		14		
Fan-Air flow rate	Cooling	Super high/High/Nom./Low/Silent operation	m ³ /min	10.68/9.78/7.68/6.06/4.68	11.10/10.14/7.98/6.54/4.68	16.38/15.00/13.32/11.82/10.62	19.92/18.54/16.56/14.34/12.36
	Heating	Super high/High/Nom./Low/Silent operation	m ³ /min	10.68/9.78/7.68/6.06/4.68	11.10/10.14/7.98/6.54/4.68	16.38/15.00/13.32/11.82/10.62	19.92/18.54/16.56/14.34/12.36
Sound pressure level	Cooling	Super high/High/Nom./Low/Silent operation	dB(A)	41/40/34/29/21	42/41/34/30/22	44/40/38/35/32	46/43/41/37/33
	Heating	High/Nom./Low/Silent operation	dB(A)	40/34/29/21	41/34/30/22	40/38/35/32	43/41/37/33
Piping connections	Liquid	OD	6.35				
	Gas	OD	9.52		12.70	15.90	
Power supply	Phase / Frequency / Voltage	Hz / V	1~ / 50 / 220-240				

(1) EER/COP according to Eurovent 2012, for use outside EU only

OUTDOOR UNIT			RXN25M	RXN35M	RXN50M	RXN60M
Dimensions	Unit	HeightxWidthxDepth	550x658x289		753x855x328	
Weight	Unit		31		44	
Compressor	Type		Hermetic swing			
Sound pressure level	Cooling	Nom.	45	46	51	
	Heating	Nom.	45	46	51	
Operation range	Cooling	Ambient	Min.~Max.	10~46		-10~46
	Heating	Ambient	Min.~Max.	-15~18		
Refrigerant	Type		R-410A			
	GWP		1,975			
Piping connections	Liquid	OD	6.35			
	Gas	OD	9.52		12.70	15.90
	Piping length	OU - IU	Max.	20		30
Power supply	Phase / Frequency / Voltage	Hz / V	1~ / 50 / 220-240			



FTXN25-35M



AP GS02 CONTROLLER



RXN25-35M

Daikin has a worldwide reputation based on 90 years' experience in the successful manufacture of high quality air conditioning equipment for residential, commercial and industrial use and 56 years as a leader in heat pump technology.

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.



Daikin products are distributed by:

FSC

ECPEN14-012