

# Wall mounted unit

ATXC-A



sensira




Energy saving during standby mode

Siesta wall mounted unit, offering good value for money and ensuring a steady supply of clean air

- › Flat, stylish front panel blends easily within any interior décor and is easier to clean
- › Quiet in operation down to 21 dBA
- › Seasonal efficiency values up to A++ in cooling
- › Choosing for an R-32 product, reduces the environmental impact with 68% compared to R-410A and leads directly to lower energy consumption thanks to its high energy efficiency

# ATXC-A + ARXC-A




Indoor unit		ATXC	25A	35A	50A	60A
Casing	Colour		White			
Dimensions	Unit	HeightxWidthxDepth	288x859x209		310x1,120x237	
Sound power level	Cooling	dB(A)	-			
	Heating	dB(A)	53	54	53	61
Sound pressure level	Heating	Super high/High/Medium/Low/	41/40/34/29/21	42/41/34/30/22	44/40/38/35/32	46/43/41/37/33

Efficiency data		ATXC + ARXC	25A + 25A	35A + 35A	50A + 50A	60A + 60A
Cooling capacity	Min./Max.	kW	1.3/3.0	1.3/3.8	2.0/6.2	1.8/6.5
Heating capacity	Min./Max.	kW	1.30/4.00	1.30/4.75	1.20/6.60	1.20/7.60
Power input	Cooling	Min./Nom./Max.	280.00/830/1,210.00	290.00/1,280/1,600.00	380.00/1,550/1,870.00	380.00/1,810/1,900.00
	Heating	Min./Nom./Max.	300.00/780/1,400.00	270.00/1,000/1,560.00	260.00/1,520/2,500.00	240.00/1,630/2,400.00
Space cooling	Capacity	Pdesign	2.56	3.37	5.48	6.24
	Energy efficiency class		A++			
	SEER		6.12	6.11	6.77	6.19
Space heating	Annual energy consumption		146	193	283	352
	Capacity	Pdesign	2.41	2.19	3.57	4.16
	Energy efficiency class		A+			
Annual energy consumption		kWh/a	773	768	1,167	1,388

Outdoor unit		ARXC	25A	35A	50A	60A
Dimensions	Unit	HeightxWidthxDepth	550x658x273		651x855x328	753x855x328
Sound power level	Cooling	dB(A)	58	60	64	65
Sound pressure level	Cooling	High	45	46	51	
Operation range	Cooling	Ambient	Min.-Max.	°CDB		
Refrigerant	Type/Charge/GWP	kg/TCO <sub>2</sub> eq	R-32/0.600/0.410/675.0	R-32/0.800/0.540/675.0	R-32/1.10/0.740/675.0	R-32/1.20/0.810/675.0
Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/220-240			

**Daikin Europe N.V.** Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · [www.daikin.eu](http://www.daikin.eu) · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN18-054

05/18



Daikin Europe N.V. participates in the Eurovent Certified Performance programme for Liquid Chilling Packages and Hydronic Heat Pumps, Fan Coil Units and Variable Refrigerant Flow systems. Check ongoing validity of certificate: [www.eurovent-certification.com](http://www.eurovent-certification.com)

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.