



Air Conditioners

Heating & Cooling



CO₂ - based VRV®

- » First VRV® system using CO₂ (R-744) as a refrigerant
- » Global warming potential = 1
- » Ozone depletion potential = 0
- » Refrigerant cycle optimised for CO₂



www.daikin.eu



RXYN10A



FXSN-A





Daikin unveils world's first CO₂-based VRV® system

Daikin Europe N.V. announces the world's first CO₂-based VRV® system. CO₂ has one of the lowest GWP¹ values (GWP=1) of all existing refrigerants, once again demonstrating Daikin's pioneering care for the environment.

The launch is one more in a series of world firsts for Daikin. As was the case with the launch of the 1st VRV® generation in the early 1980s, the launch of a CO₂-based VRV® system will lead to new installation techniques and certifications. Here again Daikin is fulfilling its pioneering role in this process, paving the way for new technologies and products. The new CO₂-based VRV® is part of Daikin's strategy to limit the impact of air conditioning on the environment and to stay ahead of environmental legislation.

Daikin is worldwide market leader in VRF systems, and intends to keep pursuing various technical challenges, such as the development of the CO₂-based VRV® system, to play a responsible role as a leader. At the same time, Daikin intends to perfect its existing HFC²-based VRV® systems, further reducing the TEWI³ impact of both ranges.


¹GWP = Global Warming Potential

²HFC = HydroFluoroCarbon (e.g.: R410A, R407C)

³TEWI: "Total Equivalent Warming Impact": sum of direct (refrigerant) and indirect (energy use) emissions of air conditioning technologies expressed in CO₂ equivalents. TEWI confirms the importance of energy efficiency and emissions reduction for air conditioning systems.


Transcritical refrigerant cycle:

For example: CO₂



Subcritical refrigerant cycle:


For example: R-410A



Transcritical refrigerant cycle


CO₂ has a very low critical temperature, so for most applications it is used in a transcritical cycle. A transcritical cycle is a cycle where a part of the process takes place at pressures above the critical point and other parts below the critical point. The critical point marks the upper limit for heat transfer processes based on evaporation or condensation. At temperatures and pressures higher than those at the critical point, there is no clear distinction anymore between liquid and vapour and it is technically challenging to control the refrigerant. Daikin is the first in the industry to use CO₂ in a VRV® system. All refrigerants have a critical point, however for conventional refrigerants this point is never reached during the entire cycle, this is called a subcritical refrigerant cycle.

System Layout



Introducing new technologies

- › **Dual Stage Intercooler (D.S.I.) circuit:** The D.S.I. circuit enables refrigerant control within the CO₂-based VRV® system and allows downsizing of the piping size.
- › **New compressor optimised for CO₂:** The CO₂-based VRV® system is equipped with two new dual swing compressors. These compressors were developed and produced by Daikin to cope with the higher pressure differentials required for the transcritical cycle of CO₂ and to reduce the leak losses.
- › **New heat exchanger:** A new three row heat exchanger and pass pattern has been developed for optimum heat exchange in the transcritical point.
- › **Expansion valve:** A new electronic expansion valve and a new four way valve have been developed to cope with the higher pressures of CO₂ (up to 12.3MPa).



Features

- › **Global Warming Potential = 1:** The Daikin CO₂-based VRV® system is the first VRF system in the market using CO₂ (R-744) as refrigerant. The GWP of CO₂ is 1, making it potentially one of the most environmental conscious refrigerants used.
- › **Ozone Depletion Potential = 0:** Like R-410A, CO₂ has no negative impact on the ozone layer when released into the atmosphere.
- › **Smaller piping diameters:** Because of the higher pressures of a CO₂ system the piping diameters are smaller. Also the amount of refrigerant in the system is lower.
- › **Automatic Test:** When refrigerant charging has ceased, pushing the test operation button on the PCB will initiate a check on the wiring, shut off valves, sensors and refrigerant volume. This test ceases automatically when completed.
- › **Night quiet mode:** For some applications the operating sound level of the outdoor unit might be too high. Therefore the sound level can be fixed, via the super silent mode, in order to avoid noise pollution.
- › **Connectable to all Daikin Control systems**

Heating & Cooling

RXYN-A			10 HP
Nominal capacity	cooling	kW	28.0
	heating	kW	31.5
COP	cooling		2
	heating		3
Dimensions	height	mm	1,680
	width	mm	930
	depth	mm	765
Weight		kg	330
Air Flow Rate (nominal at 230V)	cooling	m ³ /min	185
Refrigerant	type		R-744
	charge	kg	7.2
Piping Connections	liquid	diameter (OD) mm	9.52 (Brazed)
	gas	diameter (OD) mm	15.9 (Brazed)

Notes: Nominal cooling capacities are based on : indoor temperature : 27°CDB, 19°CWB, outdoor temperature : 35°CDB, equivalent refrigerant piping : 7.5m, level difference : 0m.
Nominal heating capacities are based on : indoor temperature : 20°CDB, outdoor temperature : 7°CDB, 6°CWB, equivalent refrigerant piping : 7.5m, level difference : 0m

FXSN-A			20	25	32	40	50	63	100	
Capacity	cooling	kW	2.2	2.8	3.6	4.5	5.6	7.1	11.2	
	heating	kW	2.5	3.2	4.0	5.0	6.3	8.0	12.5	
Power input	cooling	kW	0.110	0.110	0.114	0.127	0.143	0.234	0.242	
	heating	kW	0.090	0.090	0.094	0.107	0.123	0.214	0.222	
Dimensions	height	mm	300	300	300	300	300	300	300	
	width	mm	550	550	550	700	700	1,400	1,400	
	depth	mm	800	800	800	800	800	800	800	
Weight		kg	31	31	31	34	34	61	61	
Air Flow Rate	cooling	high	m ³ /min	9	9	9.5	11.5	15	27	28
		low	m ³ /min	6.5	6.5	7	9	11	21.5	22
External static pressure (Max)	high	Pa	88	88	64	88	88	113	107	
	standard	Pa	39	39	39	49	59	82	75	
	low	Pa	20	20	15	20	29	-	-	
Refrigerant type			R-744	R-744	R-744	R-744	R-744	R-744	R-744	

Notes: Nominal cooling capacities are based on : indoor temperature : 27°CDB, 19°CWB, outdoor temperature : 35°CDB, equivalent refrigerant piping : 7.5m, level difference : 0m.
Nominal heating capacities are based on : indoor temperature : 20°CDB, outdoor temperature : 7°CDB, 6°CWB, equivalent refrigerant piping : 7.5m (horizontal)
Capacities are net, including a deduction for cooling (an addition for heating) for indoor fan motor heat.
The external static pressure is changeable : change the connectors inside the electrical box, this pressure means : High static pressure - standard - low static pressure

BEVN-A			32	50	100
Power input	cooling	kW		0.005	
	heating	kW		0.005	
Dimensions	height	mm		140	
	width	mm		380	
	depth	mm		250	
Weight		kg		4.5	



FXSN-A



RXYN10A



Daikin's unique position as a manufacturer of air conditioning equipment, compressors and refrigerants has led to its close involvement in environmental issues. For several years Daikin has had the intention to become a leader in the provision of products that have limited impact on the environment. This challenge demands the eco design and development of a wide range of products and an energy management system, resulting in energy conservation and a reduction of waste.

VRV* products are not within the scope of the Eurovent certification programme.



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V.. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.

Daikin products are distributed by:

FSC

ECPEN10-207