

Wall mounted unit

FTX-KM



Energy saving during standby mode



Vertical auto swing



Auto fan speed



Dry programme



Titanium apatite photocatalytic air purification filter

Discreet wall mounted unit providing high efficiency and comfort

- › Discreet, stylish front panel blends easily with the wall, and matches all interior décors
- › Dry programme allows humidity levels to be reduced without variations in room temperature

- › Outdoor units are fitted with a swing compressor, renowned for its low noise and high energy efficiency
- › Outdoor units for pair application

FTX-KM




Indoor unit				FTX	25KM	35KM
Casing	Colour			White		
Dimensions	Unit	HeightxWidthxDepth	mm	285x770x225		
Sound power level	Cooling			55		
	Heating			55	56	
Sound pressure level	Cooling	High/Low/Silent operation	dBA	40/26/20		43/27/20
	Heating	High/Low/Silent operation	dBA	40/28/25		43/29/26
Control systems	Infrared remote control			ARC470A1		
	Wired remote control			BRC944B2 / BRC073A1		

Efficiency data				FTX + RX	25KM + 25KM	35KM + 35KM
Cooling capacity	Nom.			kW	2.5	3.5
Heating capacity	Nom.			kW	2.8	3.3
Power input	Cooling	Nom.			kW	1.028
	Heating	Nom.			kW	0.943
Seasonal efficiency (according to EN14825)	Cooling	Energy label		A+		
		Pdesign	kW	2.50	3.30	
		SEER		5.93	6.02	
	Annual energy consumption		kWh	148	192	
	Heating (Average climate)	Energy label		A+		
		Pdesign	kW	2.40	2.80	
SCOP/A			4.01	4.04		
Annual energy consumption		kWh	838	970		
Nominal efficiency	EER				3.54	3.21
	COP				4.01	3.71
	Annual energy consumption				353	514
	Energy label	Cooling/Heating	A/A			

Outdoor unit				RX	25KM	35KM
Dimensions	Unit	HeightxWidthxDepth	mm	550x675x284		
Sound power level	Cooling			60		
	Heating			60	62	
Sound pressure level	Cooling	High	dBA	46		48
	Heating	High	dBA	47		48
Operation range	Cooling	Ambient	Min.-Max. °CDB	10 ~46		
	Heating	Ambient	Min.-Max. °CWB	-15~18		
Refrigerant	Type/Charge/GWP	kg/TCO _{eq}		R-410A/0.70/1.5/2,087.5		R-410A/0.94/2.1/2,087.5
Power supply	Phase/Frequency/Voltage	Hz/V		1~/50/220-240		

Operation range in combination with FTX-J3: min. 10°CDB ~ max. 46°CDB | Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN16-042 08/16



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.