

Wall mounted unit

FTX-KV



Energy saving during standby mode



Online controller via app

Discreet wall mounted unit providing high efficiency and comfort

› Discreet, stylish front panel blends easily with the wall, and matches all interior décors

› Online controller: control your indoor from any location with an app, via your local network or internet

FTX-KV + RX-K




Indoor unit			FTX	20KV	25KV	35KV	50KV	60KV	71KV
Seasonal efficiency (according to EN14825)	Cooling	Energy label		A++					A
		Pdesign	kW	2.00	2.50	3.50	5.00	6.00	7.10
		SEER		6.66	6.55	6.44	6.59	6.76	5.25
	Heating (Average climate)	Annual energy consumption	kWh	105	134	190	266	311	473
		Energy label		A++			A+		A
		Pdesign	kW	2.20	2.40	2.80	4.60	4.80	6.20
Casing	Colour	Annual energy consumption	kWh	662	729	845	1,570	1,640	2,227
				White					
Dimensions	Unit	HeightxWidthxDepth	mm	286x770x225			295x990x263		
				Sound power level	Cooling	dBA	55	58	59
Sound pressure level	Cooling	High/Nom./Low/Silent operation	dBA	55	58		59	61	
				Heating	dBA	39/33/25/20	40/33/26/20	43/34/27/20	43/39/34/31
Control systems	Infrared remote control	Wired remote control	ARC480A11						
			BRC944B2 / BRC073A1			BRC944B2 / BRC073			
Refrigerant	Type	R-410							
	GWP	2,087.5							

Efficiency data			FTX + RX	20KV + 20K	25KV + 25K	35KV + 35K	50KV + 50K	60KV + 60K	71KV + 71K	
Seasonal efficiency (according to EN14825)	Cooling	Nom.	kW	2.0	2.5	3.5	5.0	6.0	7.1	
		Nom.	kW	2.50	3.00	4.00	6.00	7.00	8.20	
		Energy label		A++					A	
	Heating (Average climate)	Annual energy consumption	kWh	105	134	190	266	311	473	
		Energy label		A++			A+		A	
		Pdesign	kW	2.20	2.40	2.80	4.60	4.80	6.20	
Nominal efficiency	EER	COP	Annual energy consumption	kWh	3.98	3.78	3.43	3.58	3.65	2.61
					4.77	4.36	4.02	3.80	3.63	3.19
Energy label	Cooling/Heating							-/-		

Outdoor unit			RX	20K	25K	35K	50K	60K	71K
Dimensions	Unit	HeightxWidthxDepth	mm	550x658x275			735x870x320		
				Sound power level	Cooling	dBA	60	62	61
Sound pressure level	Cooling	High	dBA	61	62		63	66	
				Heating	dBA	46	48	47	49
Operation range	Cooling	Ambient	Min.-Max.	°CDB	-10~46				
					Heating	Ambient	Min.-Max.	°CWB	-15~18
Refrigerant	Type/Charge/GWP	R-410A/0.74/1.5/2,087.5			R-410A/1.0/2.1/2,087.5		R-410A/1.13/2.4/2,087.5		R-410A/1.45/3.0/2,087.5
		Power supply	Phase/Frequency/Voltage	Hz/V					

EER/COP according to Eurovent 2012, for use outside EU only | Nominal efficiency: cooling at 35°/27° nominal load, heating at 7°/20° nominal load
Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN16-025 03/16



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU), Fan coil units (FCU) and variable refrigerant flow systems (VRF) Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.