



# Floor standing unit

FVXS-F



Econo mode



Vertical auto swing



Weekly timer



Online controller  
via app



VRV for residential  
application

Floor standing unit for optimal heating comfort thanks to dual airflow

- › Its low height enables the unit to fit perfectly beneath a window
- › Can be installed against a wall or recessed
- › Vertical auto swing moves the discharge flaps up and down for efficient air and temperature distribution throughout the room

- › Online controller (optional): control your indoor from any location with an app, via your local network or internet

# FVXS-F + RXS-L(3)



Indoor unit		FVXS	25F	35F	50F
Casing	Colour		White		
Dimensions	Unit	HeightxWidthxDepth	600x700x210		
Sound power level	Cooling/Heating		52/52		60/60
Sound pressure level	Cooling	High/Nom./Low/Silent operation	38/32/26/23	39/33/27/24	44/40/36/32
	Heating	High/Nom./Low/Silent operation	38/32/26/23	39/33/27/24	45/40/36/32
Control systems	Infrared remote control		ARC452A1		


Efficiency data		FVXS + RXS	25F + 25L3	35F + 35L3	50F + 50L	
Cooling capacity	Min./Nom./Max.	kW	1.3/2.5/3.0	1.4/3.5/3.8	1.4/5.0/5.6	
Heating capacity	Min./Nom./Max.	kW	1.3/3.4/4.5	1.4/4.5/5.0	1.4/5.8/8.1	
Power input	Cooling	Min./Nom./Max.	0.300/0.606/0.920	0.300/1.060/1.250	0.500/1.550/2.000	
	Heating	Min./Nom./Max.	0.290/0.770/1.390	0.310/1.190/1.880	0.500/1.600/2.600	
Seasonal efficiency (according to EN14825)	Cooling	Energy label		A+		
		Pdesign	kW	2.50	3.50	5.00
		SEER		5.74	5.60	5.89
	Heating (Average climate)	Annual energy consumption	kWh	152	219	297
		Energy label		A+	A	A
		Pdesign	kW	2.60	2.90	4.20
Nominal efficiency	EER		4.12	3.30	3.23	
		COP		4.42	3.78	3.63
	Annual energy consumption	kWh	303	530	775	
		Energy label	Cooling/Heating		A/A	

Outdoor unit		RXS	25L3	35L3	50L
Dimensions	Unit	HeightxWidthxDepth	550x765x285		735x825x300
Sound power level	Cooling		59	61	62
	Heating		59	61	62
Sound pressure level	Cooling	High/Low/Silent operation	46/-/43	48/-/44	48/44/-
	Heating	High/Low/Silent operation	47/-/44	48/-/45	48/45/-
Operation range	Cooling	Ambient Min.-Max.	°CDB		-10~46
	Heating	Ambient Min.-Max.	°CWB		-15~18
Refrigerant	Type/GWP		R-410A/2,087.5		
	Charge	kg/TCO <sub>2</sub> eq	1.0/2.1	1.2/2.5	1.7/3.5
Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/220-240		1~/50/220-230-240

EER/COP according to Eurovent 2012, for use outside EU only | Nominal efficiency: cooling at 35°/27° nominal load, heating at 7°/20° nominal load

Contains fluorinated greenhouse gases

**Daikin Europe N.V.** Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-028

03/15



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU), Fan coil units (FCU) and variable refrigerant flow systems (VRF) Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.