

Air cooled mini inverter heat pump

EWYQ-ACV3/ACW1



R-410A



Inverter



Scroll compressor

- › Wide operating range
- › Built-in hydronic module: no buffer tank required and a standard pump and main switch are included

- › Easy, 'plug and play' installation
- › Single phase power supply for residential applications, three phase power supply model available for light commercial applications


EWYQ-ACV3/ACW1



Heating & Cooling		EWYQ-ACV3/ACW1			009	010	011	009	011	013
Cooling capacity	Nom.	kW			12.2 (1) / 8.60 (2)	13.6 (1) / 9.60 (2)	11.1 (2) / 15.7 (1)	12.9 (1) / 9.10 (2)	15.7 (1) / 11.1 (2)	17.0 (1) / 13.3 (2)
Heating capacity	Nom.	kW			9.90 (2) / 10.2 (1)	11.7 (1) / 11.4 (2)	13.8 (1) / 12.9 (2)	10.90 (2) / 11.20 (1)	13.2 (1) / 12.4 (2)	14.8 (1) / 13.9 (2)
Power input	Cooling	Nom.		kW	2.83 (2) / 2.85 (1)	3.28 (2) / 3.41 (1)	3.90 (2) / 4.13 (1)	3.05 (2) / 3.08 (1)	4.13 (1) / 3.90 (2)	5.18 (2) / 5.52 (1)
	Heating	Nom.		kW	2.43 (1) / 2.99 (2)	2.81 (1) / 3.46 (2)	3.20 (1) / 3.94 (2)	2.69 (1) / 3.31 (2)	3.07 (1) / 3.78 (2)	3.47 (1) / 4.27 (2)
Capacity control	Method				Inverter controlled					
EER					3.05 (2) / 4.27 (1)	2.93 (2) / 4.00 (1)	2.85 (2) / 3.79 (1)	2.99 (2) / 4.19 (1)	3.79 (1) / 2.85 (2)	2.57 (2) / 3.08 (1)
ESEER					4.31	4.30	4.33	4.43	4.44	4.36
COP					3.30 (2) / 4.19 (1)	3.29 (2) / 4.17 (1)	3.27 (2) / 4.30 (1)	3.28 (2) / 4.17 (1)	3.27 (2) / 4.31 (1)	3.25 (2) / 4.28 (1)
Space heating	Average climate water outlet 35°C	General	η _s (Seasonal space heating efficiency)	%	126	131	134	126	134	130
			SCOP	Seasonal space heating eff. class	3.22	3.34	3.41	3.22	3.41	3.30
Dimensions	Unit	Height	mm		1,435					
		Width	mm		1,420					
		Depth	mm		382					
Weight	Unit				kg					
Water heat exchanger	Type				Braze plate					
	Water flow rate	Heating	Nom.	l/min	28.3	32.6	36.9	31.2	35.5	39.8
		Water volume		l		1.01				
Air heat exchanger	Type				Hi-XSS					
Pump Standard	Nominal ESP unit	Cooling	kPa		60.5	57.8	53.2	59.2	53.2	40.9 / 45.6
		Heating	kPa		57.1	52.5	47.3	54.1	49.1	36.6 / 43.5
Hydraulic components	Expansion vessel		Volume		l					
Compressor	Type				Hermetically sealed scroll compressor					
	Quantity				1					
Fan	Type				Propeller fan					
	Quantity				2					
Fan motor	Speed	Cooling	Nom.	m ³ /min	96.0	100	97.0	-		
		Heating	Nom.	m ³ /min	90.0			-		
Sound power level	Cooling	Nom.	dBA		64.0				66.0	
		Nom.	dBA		60 (2)	64	60			
	Heating	Nom.	dBA		50					
		Nom.	dBA		50					
Night quiet mode	Cooling	dBA		45				46		
	Heating	dBA		42				43		
Operation range	Air side	Cooling	Min.~Max.	°CDB	10~46					
		Heating	Min.~Max.	°CDB	-15~35					
	Water side	Cooling	Min.~Max.	°CDB	5~20					
		Heating	Min.~Max.	°CDB	30~50					
Refrigerant	Type				R-410A					
	Circuits	Quantity		1						
		Control				Electronic expansion valve				
Refrigerant charge	Per circuit				kg		2,087.5			
					TCO ₂ eq		2.95		6.16	
Water circuit	Piping				inch		5/4"			
	Piping connections diameter				inch		G 5/4" (female)			
Power supply	Phase/Frequency/Voltage				Hz/V			1~/50/230		3N~/50/400

(1) Underfloor program: cooling Ta 35°C - LWE 18°C (Dt: 5°C); heating Ta DB/WB 7°C/6°C - LWC 35°C (Dt: 5°C) (2) Fan coil program: cooling Ta 35°C - LWE 7°C (Dt: 5°C); heating Ta DB/WB 7°C/6°C - LWC 45°C (Dt: 5°C) | Contains fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



16-421_4 02/16



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU), Fan coil units (FCU) and variable refrigerant flow systems (VRF) Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.