



Air cooled
multi-scroll
inverter chiller,
high efficiency,
reduced sound

EWAQ-GZXR



Inverter



Scroll compressor

- › High efficiency DC inverter scroll compressors
- › Advanced compressor and fan design resulting in low operating sound levels
- › Dual independent refrigerant circuit for built-in redundancy and reliable operation
- › Wide operating range in cooling mode
- › Reduced footprint thanks to the V-shaped frame


EWAQ-GZXR



Cooling only				EWAQ-GZXR	190	270	320	340	390
Cooling capacity	Nom.		kW	196	264	315	334	386	
Power input	Cooling	Nom.	kW	73.3	94.8	124	117	145	
Capacity control	Method	Stepless							
	Minimum capacity		%	14.4	14.3	14.9	14.3	14.8	
EER				2.68	2.79	2.53	2.86	2.65	
ESEER				4.88	4.95	5.05	5.07		
IPLV				5.16	5.25		5.27	5.24	
Dimensions	Unit	Height	mm	2,270	2,223				
		Width	mm	1,290	2,234				
		Depth	mm	4,450	3,560		4,460		
Weight	Unit		kg	1,618	2,124	2,180	2,430	2,536	
	Operation weight		kg	1,695	2,257	2,327	2,605	2,724	
Water heat exchanger	Type	Plate heat exchanger							
	Water flow rate	Cooling	Nom.	l/s	9.4	12.6	15.0	16.0	18.5
	Water pressure drop	Cooling	Total	kPa	26	14	15		17
	Water volume			l	29	61	75	79	92
Air heat exchanger	Type	High efficiency fin and tube type with integral subcooler							
Compressor	Type	DC Inverter Scroll							
	Quantity				6	8	10	12	
Fan	Type	Direct propeller							
	Quantity				4	6	6	8	
	Air flow rate	Nom.	l/s	15,131	22,697		30,263		
	Speed		rpm		715				
Sound power level	Cooling	Nom.	dBA	89	91			92	
Sound pressure level	Cooling	Nom.	dBA	72	74			75	
Operation range	Air side	Cooling	Min.-Max.	°CDB	-18~43				
	Water side	Cooling	Min.-Max.	°CDB	-8~20				
Refrigerant	Type / GWP	R-410A / 2,087.5							
	Circuits	Quantity		1		2			
Refrigerant charge	Per circuit		kg	48.0	36.0		48.0		
			TCO ₂ Eq	100.2	75.2		100.2		
Piping connections	Evaporator water inlet/outlet (OD)			2.5"	4.5"				
Unit	Starting current	Max	A	2					
	Running current	Cooling	Nom.	A	116	157	199	190	231
		Max	A	153	234	279	283	306	
Power supply	Phase/Frequency/Voltage			Hz/V	3~/50/400				

(1) Cooling: entering evaporator water temp. 12°C; leaving evaporator water temp. 7°C; ambient air temp. 35°C; full load operation. | Equipment contains fluorinated greenhouse gases. Actual refrigerant charge depends on the final unit construction, details can be found on the unit labels.

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-425_2 03/15



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU) and Fan coil units (FCU). Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.