



Condenserless
screw chiller,
standard
efficiency,
standard sound

EWLD-J-SS



Screw compressor

- › Compact design to allow easy indoor installation or retrofit operations
- › Daikin semi-hermetic single screw stepless compressor
- › High energy efficiency both at full and part load conditions
- › Chilled water temperatures down to -10°C on standard unit



EWLD-J-SS



Cooling only				EWLD-J-SS	110	130	145	165	235	195	265	290	310	330	360	390	430	470	500	530
Cooling capacity	Nom.			kW	110 (1)	128 (1)	142 (1)	163 (1)	236 (1)	191 (1)	264 (1)	285 (1)	306 (1)	327 (1)	355 (1)	382 (1)	428 (1)	473 (1)	501 (1)	529 (1)
Power input	Cooling	Nom.		kW	31.2 (1)	38.4 (1)	43.8 (1)	50.4 (1)	66.0 (1)	56.0 (1)	75.3 (1)	87.4 (1)	94.0 (1)	100 (1)	106 (1)	111 (1)	122 (1)	132 (1)	141 (1)	150 (1)
Capacity control	Method				Stepless															
	Minimum capacity			%	25.0															
EER					3.51 (1)	3.33 (1)	3.25 (1)	3.24 (1)	3.58 (1)	3.42 (1)	3.51 (1)	3.26 (1)	3.25 (1)	3.35 (1)	3.43 (1)	3.52 (1)	3.59 (1)	3.55 (1)	3.52 (1)	
Dimensions	Unit	Height		mm	1,020															
		Width		mm	913															
		Depth		mm	2,684															
Weight	Unit			kg	1,124	1,141	1,237	1,263	1,489	1,305	1,489	2,474	2,500	2,526	2,568	2,611	2,795		2,979	
	Operation weight			kg	1,138	1,159	1,253	1,281	1,518	1,327	1,518	2,505	2,533	2,562	2,608	2,655	2,845		3,036	
Water heat exchanger - evaporator	Type				Plate heat exchanger															
	Water volume			l	14	18	14	17	26	20	26	29	31	33	37	41	46		52	
Compressor	Water pressure drop	Cooling	Nom.	kPa	14	13	39	37	26	33	32	39	37	34	33	29	26	29	32	
	Type				Single screw compressor															
Sound power level	Quantity				1															
	Cooling	Nom.		dB(A)	89															
Sound pressure level	Quantity				2															
	Cooling	Nom.		dB(A)	94															
Operation range	Evaporator	Cooling	Min.	°CDB	-10															
			Max.	°CDB	15															
	Condenser	Cooling	Min.	°CDB	25															
			Max.	°CDB	60															
Refrigerant	Type				R-134a															
	GWP				1,430															
	Circuits	Quantity			1															
Piping connections	Condenser water inlet/outlet (OD)				-															
	Evaporator water inlet/outlet (OD)				76.2 mm															
Unit	Starting current	Max		A	151		195	288	195	288	281	293	310	403	422	440				
	Running current	Cooling	Nom.	A	52	62	72	81	107	91	120	145	153	162	171	181	197	214	227	241
		Max		A	76	97	107	122	167	143	189	215	230	245	265	286	311	335	357	378
Power supply	Phase/Frequency/Voltage			Hz/V	3~/50/400															

(1) Cooling: entering evaporator water temp. 12°C; leaving evaporator water temp. 7°C; entering condenser water temp. 30°C; leaving condenser water temp. 35°C; full load operation. Its functioning relies on fluorinated greenhouse gases

Daikin Europe N.V. Naamloze Vennootschap · Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-465_2 04/15



Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU), Fan coil units (FCU) and variable refrigerant flow systems (VRF) Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com



The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.