

## Applied Systems

# Chillers

Air cooled inverter chiller, high efficiency, standard sound

- » ESEER up to 5.24
- » Inverter stepless single screw compressor
- » High efficiency, standard sound
- » R-134a refrigerant
- » Wide operating range
- » Extensive option list
- » Low starting current
- » MicroTech III controller



# Cooling only

CAPACITY CLASS				670	740	830	900	C10	C11	C12	C13	C14	C15	C16	C17	C18							
Cooling capacity	nom.			kW			672 <sup>1</sup>	738 <sup>1</sup>	832 <sup>1</sup>	902 <sup>1</sup>	1,037 <sup>1</sup>	1,095 <sup>1</sup>	1,236 <sup>1</sup>	1,308 <sup>1</sup>	1,450 <sup>1</sup>	1,545 <sup>1</sup>	1,622 <sup>1</sup>	1,709 <sup>1</sup>	1,802 <sup>1</sup>				
Capacity control	method			Stepless																			
	minimum capacity			20												13							
Power input	cooling		nom.	kW			245 <sup>1</sup>	235 <sup>1</sup>	266 <sup>1</sup>	305 <sup>1</sup>	339 <sup>1</sup>	375 <sup>1</sup>	400 <sup>1</sup>	442 <sup>1</sup>	488 <sup>1</sup>	531 <sup>1</sup>	558 <sup>1</sup>		611 <sup>1</sup>				
EER							2.74 <sup>1</sup>	3.14 <sup>1</sup>	3.13 <sup>1</sup>	2.96 <sup>1</sup>	3.06 <sup>1</sup>	2.92 <sup>1</sup>	3.09 <sup>1</sup>	2.96 <sup>1</sup>	2.97 <sup>1</sup>	2.91 <sup>1</sup>		2.90 <sup>1</sup>	2.95 <sup>1</sup>				
ESEER							5.07	5.13	5.20	5.22	5.24	5.03	4.93	4.74	5.02	5.17	5.03	5.76	4.85				
Dimensions	unit	heightxwidthxdepth		mm			2,540x2,285x6,725	2,540x2,285x7,625	2,540x2,285x8,525			2,540x2,285x10,325			2,540x2,285x11,625		2,540x2,285x12,525		2,540x2,285x13,425		2,540x2,285x14,325		
Weight	unit			kg			5,880	6,000	6,620	6,870	7,440			8,570	8,970	9,600	9,940	11,370	12,190	12,920			
	operation weight			kg			6,140	6,250	6,860	7,110	7,880			8,960	9,360	9,980	10,320	12,220	13,040	13,790			
Water heat exchanger	type			Single pass shell & tube																			
	water volume			l			263	248	241			441			383			374		850		871	
	nominal water flow	cooling		l/s			32.00	35.20	39.70	43.00	49.50	52.30	59.00	62.40	69.20	73.70	77.40	81.50	86.00				
	nominal water pressure drop	cooling		heat exchanger		kPa			80	75	55	64	63	69	46	51	61	71	62	68	64		
Air heat exchanger	type			High efficiency fin and tube type with integral subcooler																			
Fan	air flow rate		nom.		l/s			54,188	65,025	75,863			86,700			108,376			119,213	130,051	129,454	140,143	151,129
Fan motor	speed		cooling		nom.		rpm																
Sound power level	cooling		nom.		dBA			102.1	102.2	102.5			102.9			103.5			104.1		105.8	106.0	106.2
	sound pressure level		cooling		nom.		dBA			81.0 <sup>2</sup>	81.0 <sup>2</sup>	81.1 <sup>2</sup>			81.1 <sup>2</sup>			81.2 <sup>2</sup>			82.8 <sup>2</sup>	82.9 <sup>2</sup>	
Compressor	type			Semi-hermetic single screw compressor																			
Operation range	water side		cooling		min.~max.		°CDB																
	air side		cooling		min.~max.		°CDB																
Refrigerant	type			R-134a																			
	circuits		quantity		2												3						
Refrigerant circuit	charge			kg			141	161	178			200			235			275	320	327	343	361	
Power supply	phase/frequency/voltage			Hz/V			3~/50/400																

(1) Cooling: entering evaporator water temp. 12°C; leaving evaporator water temp. 7°C; ambient air temp. 35°C; full load operation. (2) Sound pressure levels are measured at entering evaporator water temp. 12°C; leaving evaporator water temp. 7°C; ambient air temp. 35°C; full load operation; Standard: ISO3744 (3) Allowed voltage tolerance ± 10%. Voltage unbalance between phases must be within ± 3%. (4) Maximum starting current: starting current of biggest compressor + 75 % of maximum current of the other compressor + fans current for the circuit at 75 % (5) Nominal current in cooling mode: entering evaporator water temp. 12°C; leaving evaporator water temp. 7°C; ambient air temp. 35°C. Compressor + fans current. (6) Maximum running current is based on max compressor absorbed current in its envelope and max fans absorbed current (7) Maximum unit current for wires sizing is based on minimum allowed voltage. (8) Maximum current for wires sizing: (compressors full load ampere + fans current) x 1.1



EWAD-CZXS



MicroTech III




Daikin's unique position as a manufacturer of air conditioning equipment, compressors and refrigerants has led to its close involvement in environmental issues. For several years Daikin has had the intention to become a leader in the provision of products that have limited impact on the environment. This challenge demands the eco design and development of a wide range of products and an energy management system, resulting in energy conservation and a reduction of waste.



Daikin Europe N.V. participates in the Eurovent Certification programme for Air conditioners (AC), Liquid Chilling Packages (LCP) and Fan coil units (FCU). Check ongoing validity of certificate online: [www.eurovent-certification.com](http://www.eurovent-certification.com) or using: [www.certiflash.com](http://www.certiflash.com)

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.



Daikin products are distributed by: