




Wall mounted
gas
condensing
boiler

Warmly recommended: efficient, safe, economical



"We hardly notice our heating system. It is extremely quiet, easy to use, doesn't take up much space and is also very economical.

We're pleased we opted for the Daikin gas condensing boiler for our heating and hot water. Our installer recommended it and it was definitely the right choice for us."

Gas condensing technology

The best response to rising prices: efficiency

Energy is becoming increasingly precious and expensive. Choosing a boiler for your heating system is a decision affecting the next 15 to 25 years. During this time costs for your heating system will rise to a multiple of its initial investment. When investing in a new heating system, it is therefore worth giving the decision careful consideration. Gas condensing systems from Daikin are developed and manufactured according to the very latest combustion and thermal technology.

Get more from condensing technology.

State of the art condensing technology converts fuel into available heat with virtually no losses. Flue gases are cooled until the water vapour they contain has been condensed. The energy generated is used as heating energy. This makes gas condensing boilers up to 20% more efficient than standard boilers.

Optimum technology, maximum efficiency, minimum footprint – the Daikin EKOMB(G).

Thanks to energy-saving condensing technology, the Daikin EKOMB(G) achieves efficiency levels of up to 109%. The small footprint, extremely straightforward operation and installation, quiet running and maximum efficiency for domestic hot water and central heating are all features that set these Daikin gas condensing boilers apart.

Hot water at any time.

For DHW heating, you can opt for the hygienic instantaneous water heater principle or use the boiler in conjunction with the Daikin high performance domestic hot water tank for maximum DHW hygiene and convenience.

The combi boiler

Through the application of the instantaneous water heater principle, the Daikin EKOMB(G) heats DHW particularly efficiently thanks to its special 2-in-1 heat exchanger. Additional functions offer optimum convenience: the COMFORT function ensures that hot water is available quickly whenever you want it. In ECO mode, the boiler "learns" to recognise your specific hot water requirements and pre-heats the water accordingly.



Daikin EKOMB(G) – the intelligent combi boiler for domestic hot water and central heating.



Daikin EKOMB straight fins



Daikin EKOMBG labyrinth fins

Innovative heat exchangers.

The larger heat exchanger surface with labyrinth fins and an high efficiency pump increase DHW heating efficiency to 101.4% in the EKOMBG model (EKOMB model: 95.8%).



It's a matter of the right technology

Easy, convenient, individual

The Daikin EKOMB(G) offers two product ranges that can cover every demand. From the EKOMB standard model right through to the EKOMBG high efficiency class, with high efficiency high efficiency pump and larger heat exchanger surface as standard.

Convenience guaranteed

Heat exchangers in the EKOMB(G) models come with a Daikin 10-year guarantee.

Quick installation and maintenance

The mounting rail, available as an option, with pre-assembled expansion vessel and all necessary connection valves ensures quick and easy installation in the smallest of spaces. The compact product design, with just a small number of individual parts not only increases the reliability of the boiler, but also reduces the usual maintenance costs. All individual parts, are easily accessible, making maintenance easier too.

User benefits

- › Energy-saving condensing technology with efficiency levels of up to 109%
- › Maximum efficiency thanks to the 2-in-1 heat exchanger (in every combi boiler)
- › Copper pipes in the heat exchanger for a long service life
- › Extremely convenient technology in the smallest of spaces
- › Very quiet operation
- › With 3-way valve, ideal for use in conjunction with thermal stores
- › 10-year guarantee on the heat exchanger

	Daikin EKOMB	Daikin EKOMBG
Heat exchanger	Straight fins	Labyrinth fins
Circulation pump	High efficiency pump	High efficiency pump
DHW heating efficiency	95.8%	101.4%

Two product ranges – but always the first choice

The gas condensing boiler is available in two different versions:

- › The EKOMB models are a simple introduction to efficient gas condensing technology.
- › The EKOMBG models offer maximum convenience and maximum efficiency – without compromise



DHW heating up to 30% more efficient

The special 2-in-1 heat exchanger of the Daikin EKOMB(G) gas condensing boiler is used for central heating and DHW heating. Because it heats the domestic hot water directly, employing the hygienic instantaneous water heater principle, the appliance still operates within the condensing range for DHW heating. This leads to an increase in efficiency of up to 30% compared to conventional gas condensing boilers.



Specification

Indoor Unit				EKOMBG			EKOMB			
				22A	28A	33A	22A	28A	33A	
Gas	Consumption (G20)	Min-Max	m ³ /h	0.57-2.42	0.75-3.02	0.78-3.39	0.58-2.29	0.74-2.46	0.75-3.39	
	Consumption (G31)	Min-Max	m ³ /h	0.22-0.92	0.28-1.15	0.30-1.29	0.22-0.87	0.28-0.94	0.28-1.29	
	Connection	Diameter	mm	15						
Central heating	Heat input Q _n (net calorific value)	Nom	Min-Max	kW	5.5-23.3	7.2-29.1	7.5-32.7	5.6-18.7	7.1-23.7	7.2-27.3
	Heat input Q _n (gross calorific value)	Nom	Min-Max	kW	6.1-25.9	8.0-32.3	8.3-36.3	6.2-20.8	7.9-26.3	8.0-30.3
	Output P _n at 80/60°C	Min-Nom		kW	5.4-22.7	7.1-28.4	7.4-32.1	5.4-17.8	6.9-22.8	7.1-26.3
	Output P _n at 50/30°C	Min-Nom		kW	5.9-23.8	7.7-31.1	8.2-35.0	5.9-18.5	7.6-23.4	7.8-27.1
	Output at 40/30°C	Min		kW	5.9	7.7	8.2	6.0	7.6	7.7
	Water pressure (PMS)	Max		bar	3					
	Water temperature	Max		°C	90					
Domestic hot water	Efficiency	Net calorific value	%	107		109	107			
	Heat input (net calorific value) Q _n	Nom	Min-Max	kW	5.5-23.3	7.2-29.1	7.5-32.7	5.6-22.1	7.1-28.0	7.2-32.7
	Heat input (gross calorific value) Q _n	Nom	Min-Max	kW	6.1-25.9	8.0-32.3	8.3-36.3	6.2-24.6	7.9-31.1	8.0-36.3
	Output	Min-Nom		kW	5.9-22.7	7.7-28.4	8.2-32.1	6.1-21.0	6.6-26.2	7.9-31.5
	Domestic hot water threshold			l/min	1.5					
	Water flow	Rate	Nom	l/min	10 (1) / 6 (2)	12.5 (1) / 7.5 (2)	15 (1) / 9 (2)	10 (1) / 6 (2)	12.5 (1) / 7.5 (2)	15 (1) / 9 (2)
Supply air	Temperature	Factory setting	°C	60						
	Connection		mm	100						
Flue gas	Concentric			Yes						
	Connection		mm	60						
Casing	Colour			White - RAL9010						
	Material			Precoated sheet metal						
Dimensions	Unit	Height x Width x Depth	mm	590x450x240	650x450x240	710x450x240	590x450x240	650x450x240	710x450x240	
Weight	Unit	Empty	kg	30	33	36	30	33	36	
Power supply	Phase/Frequency/Voltage		Hz/V	1~/50/230						
Electrical power consumption	Max.		W	80			80			
	Standby		W	2						

(1) Setpoint 40°C (2) Setpoint 60°C

Our promise...

... is to ensure that customers can depend on Daikin for the ultimate in comfort, so that they are free to focus on their own working and home lives.

We promise to dedicate ourselves to technological excellence, a design focus and the highest quality standards so that our customers can trust and rely on the comfort we deliver.

Our promise to the planet is absolute. Our products are at the forefront of low energy-usage and we will innovate to further reduce the environmental impact of HVACR (Heating, Ventilation, Air conditioning, Refrigeration) solutions.

We lead where others follow. We will continue our global leadership in HVACR solutions as our specialist expertise in all market sectors combined with 90 years' experience enable us to deliver added value in long-lasting relationships based on trust, respect and credibility.

We promise to continue our forward-thinking ethos, treating challenges as opportunities to produce ever-better solutions. We will drive innovation and go the extra distance for our customers and our company.

We will be smart and ready to do things differently. We will deliver on these core values of our brand and enjoy sustainable success with continued growth.

Daikin Europe N.V. Naamloze Vennootschap Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)



ECPEN15-710

XXX - 04/15



The present publication is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this publication to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this publication. All content is copyrighted by Daikin Europe N.V.

The present publication supersedes ECPEN14-115. Printed on non-chlorinated paper. Prepared by La Movida, Belgium.