



Decarbonisation of buildings made easy

VRV 5 Heat Pumps

① FLEXIBLE |


Heat pump technology to fit any commercial building

- Extensive piping lengths and heights to meet any VRV application
- Quiet operation via 5 low sound steps, bringing sound pressure down to 41 dB(A)
- Wide operation range down to -20°C in heating and up to +46°C in cooling
- Continuous heating during defrost makes VRV 5 an ideal monovalent heating solution

② SUSTAINABLE |

Significantly reduces the CO2 footprint of your building

- Reduced indirect impact thanks to high seasonal efficiency
 - $\eta_{s,c}$ up to 298.3%, measured with most popular units
 - Reduces running costs compared to traditional systems
- Reduced direct impact thanks to lower GWP R-32 refrigerant
 - Up to 71% Global Warming Potential reduction compared to R-410A
 - Single component refrigerant, easy to recover and reuse
 - Reduced leak check requirement in line with F-gas (only 1 inspection/year up to 74kg of total charge)



22.4 kW ~ 56.0 kW 25.0 kW ~ 63.0 kW

Find out all the details on the new VRV 5 Heat Pump in our webinar



③ UNIQUE SHĪRUDO TECHNOLOGY | Provides peace of mind

- Suitable for any room size: ShĪrudo Technology allows the easy installation of R-32 VRV in any room
- Maximum installation flexibility, thanks to factory-provided refrigerant control measures
- No need for complex studies or field supplied equipment
- 3rd party certification according to the product standard IEC60335-2-40



Find out more about refrigerant safety standards and ShĪrudo Technology



④ SUPPORT | Wide network of experts with specialised advice

- Maximise BREAAAM/LEED score
- Extra credit thanks to lower GWP of R-32
- Our accredited professionals assist to optimize the design

Our online support software with visual floorplan interface makes design easy and ensures compliance with product standards



⑤ WIDEST R-32 PORTFOLIO | Match any application

- Widest range of specifically designed indoor units and air curtains: 11 unit models in 96 variations
- Plug & play ventilation solutions from 150 up to 140.000 m³/h
- Extensive range of intuitive controllers:
 - Individual or centralized
 - On-premises or in the Cloud



..... CONTROLLERS



..... INDOOR

..... VENTILATION

SPECIFICATIONS

	Module	Single Units								Multi combinations (continuous heating)					
		RXMA5A	RXYA8A	RXYA10A	RXYA12A	RXYA14A	RXYA16A	RXYA18A	RXYA20A	RXYA10A	RXYA13A	RXYA16A	RXYA18A	RXYA20A	
System	Outdoor unit 1 Outdoor unit 2									RXMA5A RXYA8A	RXMA5A RXYA8A	RXYA8A RXYA8A	RXYA8A RXYA10A	RXYA8A RXYA12A	
Capacity range		5	8	10	12	14	16	18	20	10	13	16	18	20	
Cooling capacity	Prated,c	14.0	22.4	28.0	33.5	40.0	45.0	50.4	56.0	28	36.4	44.8	50.4	55.9	
Heating capacity	Prated, h		22.4	28.0	33.5	40.0	45.0	50.4	56.0	28	36.4	44.8	50.4	55.9	
	Max.		25.0	31.5	37.5	45.0	50.0	56.5	63.0	32	41	50	46.5	62.5	
Recommended combination		Only for use in multi combinations								3xFXFAS0A2VEB + 4xFXFAG3A2VEB + 4xFXFAS0A2VEB + 10xFXFAS0A2VEB					
SEER			7.26	7.06	7.04	7.67	6.99	6.87	6.52	7.55	7.42	7.12	7.18	7.16	
SCOP			4.11	4.33	4.49	4.28	4.26	4.39	4.14	4.09	4.11	4.35	4.34	4.38	
η _{s,c}			287.3%	279.3%	278.7%	302.2%	276.6%	271.6%	257.6%	299.1%	293.8%	281.9%	284.1%	283.2%	
η _{s,h}			161.5%	170.2%	176.4%	168.3%	167.5%	172.5%	162.7%	160.6%	161.5%	170.9%	170.5%	172.2%	
Dimensions	HxWxD	1685x930x765						1685x1240x765							
Weight		214			297			320							
Sound power level	Cooling	78.3	78.3	78.8	82.5	79.5	83.7	83.4	87.9	81.3	81.3	81.3	81.6	83.9	
	Heating	79.4	79.4	80.7	83.3	82.9	86.3	85.1	89.6						
Sound pressure level	Cooling	56.3	56.3	58.0	60.8	59.0	61.6	63.0	67.0	59.3	59.3	59.3	60.2	62.1	
	Heating														
Operation range	Cooling/Heating	Min/Max °C													
Refrigerant	Type/GWP	R-32 / 675.0													
	Charge	6.08/9.0								7.16/10.6					
Piping connections	Liquid OD	9.5	9.5	9.5	12.7	12.7	12.7	12.7	12.7	9.5	12.7	12.7	12.7	12.7	
	Gas OD	19.1	19.1	19.1	22.2	22.2	28.6	28.6	28.6	19.1	22.2	28.6	28.6	28.6	
	Equilizing pipe														
	Total piping length	System actual	1000						500						
Power supply	Phase/Frequency/ Voltage	3N~/50/380-415													
Current - 50Hz	Maximum fuse amps (MFA)	20	20	25	32	32	40	40	50	40	40	40	50	50	

Access all technical details here



Daikin Europe N.V. Naamloze Vennootschap Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Publisher)



Daikin Europe N.V. participates in the Eurovent Certified Performance programme for Liquid Chilling Packages and Hydronic Heat Pumps, Fan Coil Units and Variable Refrigerant Flow systems. Check ongoing validity of certificate: www.eurovent-certification.com



ECPEN23-233 10/2023
Printed on non-chlorinated paper.