

AZX6CABLEBUS [10/100/500]

Airzone bus cable

Description

Flexible shielded twisted cable. It is used to transmit data, analogic and digital signal and also to supply Airzone elements. It is supplied in 10, 100 and 500-meter cable reels.



Technical specs

| | |
|------------------------------|---|
| Section | Communication: 2 x 0.22 mm ² (Blue-Green) Power supply: 2 x 0.50 mm ² (Red-Black) |
| Conductor | 0.5 mm ² : Class 5 Polished copper s/UNE EN 60228 0.22 mm ² : Polished copper (7 x 0,20 mm) |
| Insulation | 0.5 mm ² : PVC/A Ø1,9 mm 0.22 mm ² : PVC/A Ø1 mm |
| Operating voltage | 300 V |
| AC voltage test | 1000 V |
| Maximum admissible intensity | 3,5 A (Ø 0,5 mm ²) |
| Maximum resistance at 20°C | 0.5 mm ² : 39 Ω/Km 0.22 mm ² : 82,7 Ω/Km |
| Materials | Conductor: Polished copper Insulation: PVC/A Jacket: PVC/ST2 Cable shield: Polyester + Tinned copper drainage + Aluminum/Polyester |